


# Batch Validation Certificate

<b>Partnumber:</b>	K1241BD
<b>Description:</b>	CELL BODY 0.01/CM 1-NPT
<b>Batch Number:</b>	BV201005001 
<b>Qty:</b>	10
<b>Date:</b>	26-Jan-10

## Part Requirements

Electrode manufactured from Stainless Steel 316L with a surface roughness of  $Ra < 3.2\mu m$

### A. Material

Copied from the Material Certificate 3.1 (EN 10204) accompanying this raw material from the supplier.

Manufacturer	Diameter	Grade	Heatnumber	Trade name:
OLARRA	HEX 36	1.4404 MECA	950030	

### B. Surface roughness

Surface roughness was established by measurement using a Tailor Hobson Surtronic 3+ Surface Tracing device. Serial Number 1167L.

A number of individual parts were taken from the batch and subjected to measurement. Batch compliance was accepted or rejected according to ISO 2829.

Required Surface Roughness	$Ra < 3.2\mu m$
Established Surface Roughness	Complies to $Ra < 3.2\mu m$

Inspector:

S 09

Signed:

