


# Batch Validation Certificate

<b>Partnumber:</b>	82852592
<b>Description:</b>	INNER ELECTRODE SANDBLASTED
<b>Batch Number:</b>	BV201007004 
<b>Qty:</b>	20
<b>Date:</b>	10-Feb-10

## Part Requirements

Electrode manufactured from 316L with a surface roughness of  $Ra < N.A.\mu m$

### A. Material

Copied from the Material Certificate 3.1 (EN 10204) accompanying this raw material from the supplier.

Manufacturer	Diameter	Grade	Heatnumber	Trade name:
OLARRA	Ø 12 MM	1.4404 MECA	945774	

### B. Surface roughness

Surface roughness was established by measurement using a Tailor Hobson Surtronic 3+ Surface Tracing device. Serial Number 1167L.

A number of individual parts were taken from the batch and subjected to measurement. Batch compliance was accepted or rejected according to ISO 2829.

Required Surface Roughness	$Ra < N.A.\mu m$
Established Surface Roughness	Complies to $Ra < N.A.\mu m$

Inspector:

S 05

Signed:

