

Simple! Compact Size! Ready to Run!

MW100 Quick Start Package

- Real-time data monitoring with a web browser
- Universal inputs (DCV/TC/RTD/DI)
- 100 ms scan speed
- Multi-interval measurement and logging to high capacity Compactflash media
- Email messaging and file transfer via FTP

Model	Suffix Code	Added Specifications Code	Description
MW100			Main module *1,2
Language	-E		English (comes with MW100 Viewer Software)
Supply voltage	-1		100 VAC-240 VAC
	-2		12 to 28 VDC, with AC adapter *3
	-3		12 to 28 VDC, without AC adapter *4
Power input type and power supply cord		<input type="checkbox"/>	Power supply code
Options		/C2	RS-232 communication interface *5,6
		/C3	RS-422-A/485 communication interface *5,6
		/M1	MATH functions *6,7
Quick Start Package		/SL1	10 ch Quick Start Package
		/SL2	20 ch Quick Start Package
		/SL3	30 ch Quick Start Package

*1 CF (compact flash) card not included. *2 Modbus/TCP function comes standard. *3 "W" cannot be selected with "-2". *4 With "-3, only W (screw terminal) can be selected. *5 /C2 and /C3 cannot be selected together. *6 /C2 or /C3 must be selected when using the Modbus/RTU slave function. Also, /M1 must be selected for use of the Modbus/RTU master function. *7 /M1 must be selected when using the Modbus/TCP client function.




Fast set up- attach sensors, connect to your network, configure with your web browser, and you are ready to measure and record data- no special software needed. Built-in data logging to high capacity Compact Flash media



Integrated Data Acquisition Software Package

DAQ LOGGER

Supports a wide range of recorders, data loggers, controllers, and measuring instruments. Data acquisition systems comprising diverse models can be set up without programming.



Main Functions

- Data acquisition and recording on up to 1600 channels at 1 second intervals (shortest)
- Real time monitoring of up to 50 groups of 32 channels
- Data acquisition systems allowing connections with up to 32 units of differing models
- Saved data can be redisplayed, printed, converted to other formats, and appended with comments

*A CF card, Ethernet cable, and PC are not included in the MX100/MW100 Quick Start Package, so they need to be obtained separately.

*DAQMASTER is a registered trademark of Yokogawa Electric Corporation. Microsoft Windows, IE, Internet Explorer, and logo mark are registered trademarks of Microsoft Corporation in the United States.

*Company and product names that appear in this manual are trademarks or registered trademarks of their respective holders.