

# General Specifications

## List of RoHS Directive Compliant Products

### GS 04A01A01-00EN

#### ■ Overview

This is a list of recorder and controller products that support the RoHS directive.

Meanings of the symbols used in the table to indicate the RoHS directive compliance status.

- ◎ RoHS directive compliant product
- RoHS directive compliance in future
- [Blank] RoHS directive compliance under consideration
- X No plan for RoHS directive compliance

NOTE: Maintenance and Repair

Some supplied parts may not support RoHS. Please note that if such parts are used in the maintenance or repair of a product, that product may no longer be RoHS-compliant.

Table Range: Currently sold products and products whose order acceptance was discontinued during or after September, 2005

Category	Product Name	Model	RoHS Directive Compliance Status	Start of Manufacture	Remarks
CX1000/CX2000 series	DAQSTATION CX1000	CX1x0x	x	-	
	DAQSTATION CX2000	CX2xx0	x	-	
DX1000/DX2000 series	Daqstation DX1000	DX10xx	◎	2009/9/30	Excluding. Remote control for /KB
	Daqstation DX1000N	DX10xxN	◎	2009/9/30	Excluding. Remote control for /KB
	Daqstation DX2000	DX20xx	◎	2009/9/30	Excluding. Remote control for /KB
	Daqstation DX364	DX364			
DX100/DX200 series	DAQSTATION DX100	DX1xx	x	-	2009/12/29: Discnt. of Order Accept.
	DAQSTATION DX200	DX2xx	x	-	2009/12/29: Discnt. of Order Accept.
	DAQSTATION DX100P	DX1xxP	x	-	2011/03/31: Discnt. of Order Accept.
	DAQSTATION DX200P	DX2xxP	x	-	2011/03/31: Discnt. of Order Accept.
	DAQSTATION Special Housing model DX100L	DX1xxL	x	-	2009/12/29: Discnt. of Order Accept.
	DAQSTATION Circular display model DX200C	DX20xC	x	-	2007/06/29: Discnt. of Order Accept.
Input Terminal	Input Terminal for DX-P	438227	x	-	
FX1000	Paperless Recorder	FX10xx	◎	2011/11/30	
FX100 series	Paperless Recorder FX100	FX1xx	◎	2010/2/26	Excluding. -1 (FDD model)
AX100 series	AX100	AX1xx	x	-	2008/11/30: Discnt. of Order Accept.
	Shunt Resister for Screw Input Terminal	415930	x	-	2009/04/29: Discnt. of Order Accept.
		415931	x	-	2008/12/05: Discnt. of Order Accept.
		415932	x	-	2008/12/05: Discnt. of Order Accept.
	3.5inch Floppy disk	415933	x	-	2008/12/05: Discnt. of Order Accept.
Mounting Bracket	415934	x	-	2008/12/05: Discnt. of Order Accept.	
μR10000/μR20000 series	μR10000 Recorder	43610x	◎	2009/9/30	/H2 under consideration
	μR20000 Recorder	4371xx	◎	2009/9/30	/H2 under consideration
	RXA10 Configuration Software	RXA10			
μRS1000/μRS1800 series	μRS1000 Recorder	4365xx	x	-	2011/03/31: Discnt. of Order Accept.
	μRS1800 Recorder	4375xx	x	-	2011/03/31: Discnt. of Order Accept.
	Setting Software	437902	x	-	2011/03/31: Discnt. of Order Accept.
	Setting Display for μRS1000	437903	x	-	2011/03/31: Discnt. of Order Accept.
	Setting Display for μRS1800	437904	x	-	2011/03/31: Discnt. of Order Accept.
μR1000/μR1800 series	μR1000 Recorder	43600x	x	-	2005/09/30: Discnt. of Order Accept.
	μR1000 Special Housing	43602x	x	-	2005/09/30: Discnt. of Order Accept.
	μR1800 Recorder	4370xx	x	-	2006/05/31: Discnt. of Order Accept.

Category	Product Name	Model	RoHS Directive Compliance Status	Start of Manufacture	Remarks
SR series	SR10000 Recorder	SR1000x	☉	2009/9/30	
	SR1000 Recorder	SR100x	×	-	2006/09/30: Discnt. of Order Accept.
	SR10 Recorder	SR1x	×	-	2006/09/30: Discnt. of Order Accept.
Shunt Resistor	Shunt Resistor for Screw Input Terminal	41592x			
	Shunt Resistor for Clamped Input Terminal	43892x			
X-Y Recorder series	A3 X-Y Recorder	3023x3	×	-	2007/01/26: Discnt. of Order Accept.
	A3 X-Y Recorder	3024x3	×	-	2007/01/26: Discnt. of Order Accept.
	A4 X-Y Recorder	3025x3	×	-	2007/01/26: Discnt. of Order Accept.
Portable Recorder	Portable Recorder	3057xx	×	-	2007/09/28: Discnt. of Order Accept.
LR series	LR8100E Recorder	3701xx	×	-	
	LR12000E Recorder	3702xx	×	-	
	LR4110E Recorder	3711xx	×	-	
	LR4120E Recorder	3712xx	×	-	
	LR4210E Recorder	3721xx	×	-	
	LR4220E Recorder	3722xx	×	-	
	Rack Mount Adapter	37898x	×	-	
IC Memory Card	IC Memory Card (Setting Data), 8k bytes	378901	×	-	
	IC Memory Card (128k bytes)	378903	×	-	
	IC Memory Card (512k bytes)	378905	×	-	
	IC Memory Card (1M Bytes)	378906	×	-	
DARWIN series	DA100 Data Acquisition Unit	DA100	×	-	
	DC100 Data Acquisition unit	DC100	×	-	2009/09/30: Discnt. of Order Accept.
	DR130 Hybrid Recorder	DR130	×	-	
	DR230 Hybrid Recorder	DR23x	×	-	
	DR240 Hybrid Recorder	DR24x	×	-	
	DA100 Data Acquisition Subunit	DS400	×	-	
	DA100 Data Acquisition Subunit	DS600	×	-	
	DI/DO Terminal Module	DT100	×	-	
	Alarm Relay Output Module	DT200	×	-	
	Communication Interface Module	DT300	×	-	
	Retransmission Module	DT500	×	-	
	Universal Inputs Module	DU100	×	-	
	DCV/TC/DI Inputs Module	DU200	×	-	
	mA Inputs Module	DU300	×	-	
	Power Monitor Module	DU400	×	-	
	10ch Strain Input Module	DU500	×	-	
	Pulse Input Module	DU600	×	-	
	Digital Input Module	DU700	×	-	
	EMR Inputs Module	DU900	×	-	
	10CH EMR Inputs Module	DU910	×	-	
	Extension Module/Extension Base Unit	DV100	×	-	
	Remote Display Unit	DV120	×	-	2005/12/29: Discnt. of Order Accept.
	Extension Cable	DV200	×	-	
	Cable Adapter	DV250	×	-	
	Shunt Resistor	DV300	×	-	
	Rack Mounting Kits etc.	DV400	×	-	
	Strain Conversion Cable	DV450	×	-	
AC Adapter Cable	DV500	×	-		
MV1000/ MV2000 series	MVAdvanced MV1000	MV10xx	☉	2009/9/30	
	MVAdvanced MV2000	MV20xx	☉	2009/9/30	
	Carrying soft case	790501			

Category	Product Name	Model	RoHS Directive Compliance Status	Start of Manufacture	Remarks
MV100/ MV200 series	MobileCorder MV100	MV1xx	×	-	2009/05/29: Discnt. of Order Accept.
	MobileCorder MV200	MV2xx	×	-	2009/05/29: Discnt. of Order Accept.
	Front cover	790502	×	-	2009/05/29: Discnt. of Order Accept.
	Cover	790511	×	-	2009/05/29: Discnt. of Order Accept.
	Module removal handle	790581	×	-	2009/05/29: Discnt. of Order Accept.
MW100/ MX100 series	MW100 Data Acquisition unit	MW100	◎	2010/2/26	Excluding. MW100-x-2x (Model with AC Adapter)
	MX100 Data Acquisition unit	MX100	◎	2010/2/26	
	Data Acquisition module for MX/MW	MX110	◎	2010/2/26	
	Data Acquisition module for MX/MW	MX112	◎	2010/2/26	
	PLUSE INPUT MODULE	MX114	◎	2010/2/26	
	Data Acquisition module for MX/MW	MX115	◎	2010/2/26	
	CAN Bus Module	MX118			
	Analog output module for MX/MW	MX120			
	Digital output module for MX/MW	MX125	◎	2010/2/26	
	Data Acquisition base plate for MX/MW	MX150	◎	2010/2/26	
	DAQMASTER STYLE UP KIT	772050			
	External M4 screw terminal block	772061			
	Connection cable	772062			
	Plate with clamp terminals	772063			
	Clamp terminal	772064			
	Clamp terminal	772065			
	Connector cover for base plate	772066			
	Plate with clamp terminals	772067			
	Plate with clamp terminals	772068			
	Plate with clamp terminals	772069			
	AC Adapter for MW100	772075			
	Plate with screw terminals(M3,RJC)	772080			
	Plate with clamp terminals(10 ohm)	772081			
	Plate with clamp terminals(100 ohm)	772082			
	Plate with clamp terminals(250 ohm)	772083			
	Adapter for Compactflash memory card	772090			
	Compactflash memory card, 128MB	772091			2010/08/31: Discnt. of Order Accept.
Compactflash memory card, 256MB	772092			2010/01/05: Discnt. of Order Accept.	
Compactflash memory card, 512MB	772093				
Compactflash memory card, 1GB	772094				
Compactflash memory card, 2GB	772095				
OR100E/ OR300E series	Handy Oscillographic Recorder OR100E	OR1x2	×	-	2008/12/29: Discnt. of Order Accept.
	Handy Oscillographic Recorder OR300E	OR3x2	×	-	2008/12/29: Discnt. of Order Accept.
	AC Adapter	788011	×	-	2008/12/29: Discnt. of Order Accept.
	Rechargeable Battery Pack	788021	×	-	2008/12/29: Discnt. of Order Accept.
	Logic Probe	788031	×	-	2008/12/29: Discnt. of Order Accept.
	Logic Probe	788035	×	-	2008/12/29: Discnt. of Order Accept.
	Temperature adapter	788041	×	-	2008/12/29: Discnt. of Order Accept.
	Carrying Case	788081	×	-	2008/12/29: Discnt. of Order Accept.
	Compact Case	788082	×	-	2008/12/29: Discnt. of Order Accept.
	Measurement Lead (for Safety Terminal)	366963	×	-	
SolStation	Application Specific Controller	HXS10	◎	2010/7/23	
Wireless transmitters	Multi-input temperature transmitter	YTMX580			

Category	Product Name	Model	RoHS Directive Compliance Status	Start of Manufacture	Remarks
UTAdvanced series	Digital Indicating Controller	UT55A	◎	2009/5/28	
	Digital Indicating Controller	UT52A	◎	2009/5/28	
	Digital Indicating Controller	UT35A	◎	2010/1/29	
	Digital Indicating Controller	UT32A	◎	2010/1/29	
	Program Controller	UP55A	◎	2010/8/30	
	Program Controller	UP35A	◎	2010/9/24	
	Digital Indicator with Alarms	UM33A	◎	2010/8/30	
	Parameter Setting Software	LL50A	◎	2009/5/28	
GREEN series	Digital Indicating Controller	US1000	×	-	
	Digital Indicating Controller	UT750	◎		Compliant with TOKUCHU /Z113
	Digital Indicating Controller	UT551	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Digital Indicating Controller	UT550	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Digital Indicating Controller	UT520	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Digital Indicating Controller	UT450	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Digital Indicating Controller	UT420	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Digital Indicating Controller	UT351	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Limit Controller	UT350L	×	-	
	Digital Indicating Controller	UT350	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Digital Indicating Controller	UT321	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Digital Indicating Controller	UT320	◎		Compliant with TOKUCHU /Z113 2010/09/30: Discnt.of Order Accept.
	Program Controller	UP750	◎		Compliant with TOKUCHU /Z113
	Program Controller	UP550	◎		Compliant with TOKUCHU /Z113
	Program Controller	UP351	◎		Compliant with TOKUCHU /Z113 2011/03/31: Discnt.of Order Accept.
	Program Controller	UP350	◎		Compliant with TOKUCHU /Z113 2011/03/31: Discnt.of Order Accept.
	Digital Indicator with Alarms	UM351	◎		Compliant with TOKUCHU /Z113 2011/03/31: Discnt.of Order Accept.
	Digital Indicator with Alarms	UM350	◎		Compliant with TOKUCHU /Z113 2011/03/31: Discnt.of Order Accept.
	Digital Indicator with Alarms	UM331	◎		Compliant with TOKUCHU /Z113 2011/03/31: Discnt.of Order Accept.
	Digital Indicator with Alarms	UM330	◎		Compliant with TOKUCHU /Z113 2011/03/31: Discnt.of Order Accept.
	Manual Setters	UD350	◎	2011/4/26	
	Manual Setters	UD320	◎	2011/4/26	
	Manual Setters	UD310	◎	2011/4/26	
	PC-Based Custom Computation Building Tool	LL1200	×	-	
	PC-based Parameters Setting Tool	LL1100	×	-	
	PC-based Custom Computation Building Tool	LL200	◎		Compliant with TOKUCHU /Z115
	PC-based Parameters Setting Tool	LL100	◎		Compliant with TOKUCHU /Z115

Category	Product Name	Model	RoHS Directive Compliance Status	Start of Manufacture	Remarks
UT100 series	Temperature Controller	UT155	◎	2011/4/26	Compliant with TOKUCHU /Z59 till Apr. 26, 2011.
	Temperature Controller	UT152	◎	2011/4/26	Compliant with TOKUCHU /Z59 till Apr. 26, 2011.
	Temperature Controller	UT150	◎	2011/4/26	Compliant with TOKUCHU /Z59 till Apr. 26, 2011.
	Temperature Controller	UT130	◎	2011/4/26	Compliant with TOKUCHU /Z59 till Apr. 26, 2011.
	Limit Controller	UT150L	◎	2011/4/26	
	Program Temperature Controller	UP150	◎	2011/4/26	Compliant with TOKUCHU /Z59 till Apr. 26, 2011.
Single-loop Controllers	YS80 Series	-	×	-	
	YS100 Series	-	×	-	
	YS1000 Series	-	×	-	
Power Monitors	UPM100/101 Series	-	×	-	
	PR300 Series	-	×	-	
Signal Conditioners	VJ Series	-	×	-	
	M Series	-	×	-	
	D Series	-	×	-	
	R Series	-	×	-	
	F Series	-	×	-	
	W Series	-	×	-	
	P Series	-	×	-	
	G Series	-	×	-	
	H Series	-	×	-	
	Presision resistance	X010	◎	2008/4/30	X010 with yellow tube cover is complying with RoHS.
Surge Arresters	AR Series	-	×	-	
	AR1 Series	-	×	-	