

# General Specifications

## EJX-A Series and EJA-E Series Explosion Protected Type and Marine Certificate Type



GS 01C25A20-01EN

### ■ Outline

In this General Specifications, EJX-A Series and EJA-E Series optional specifications for some explosion protected types and marine certificate types are stated. For standard specifications, functions, and other optional specifications, please refer to the standard General Specifications of each model.

### ■ Model

EJX□□□A and EJA□□□E

### ■ Explosion Protected Type

Item	Description	Code
NEPSI	NEPSI Flameproof Approval *1*2*5*6 Applicable Standard: GB3836.1-2010, GB3836.2-2010 Ex d IIC T4 ~ T6 Gb Enclosure: IP66 / IP67 Max. Process Temp.: T4; 120°C (248°F), T5; 100°C (212°F), T6; 85°C (185°F) Ambient Temp.: -50 to 75°C (-58 to 167°F) for T4, -50 to 80°C (-58 to 176°F) for T5, -50 to 75°C (-58 to 167°F) for T6	NF2
	NEPSI Intrinsic safety Approval for HART/BRAIN Protocol Type *1*2*3*4 Applicable Standard: GB3836.1-2010, GB3836.4-2010, GB3836.20-2010 Ex ia IIC T4 Ga Ambient Temp.: -50 to 60°C (-58 to 140°F) Max. Process Temp.: 120°C (248°F) Electrical Parameters: Ui=30 V, Ii=200 mA, Pi=0.9 W, Ci=27.6 nF, Li=0 μH	NS21
	NEPSI Intrinsic safety Approval for Fieldbus Type *1*3*4*5 Applicable Standard: GB3836.1-2010, GB3836.4-2010, GB3836.19-2010, GB3836.20-2010 Ex ia IIC/IIB T4 Ga Ambient Temp.: -40 to 60°C (-40 to 140°F) Max. Process Temp.: 120°C (248°F) Electrical parameters: [Entity] Ui = 24 V, Ii = 250 mA, Pi = 1.2 W, Ci = 3.52 nF, Li = 0 μH [FISCO IIC] Ui = 17.5 V, Ii = 380 mA, Pi = 5.32 W, Ci = 3.52 nF, Li = 0 μH [FISCO IIB] Ui = 17.5 V, Ii = 460 mA, Pi = 5.32 W, Ci = 3.52 nF, Li = 0 μH	NS25
KOSHA	KOSHA Flameproof Approval *1*2*5*6 Applicable Standard: Notice of Ministry of Labor No. 2010-36, EN 60079-0:2009, EN 60079-1:2007 Ex d IIC T4, T5, T6 Amb. Temp. (Tamb): T4; -50 to 75°C, T5; -50 to 80°C, T6; -50 to 75°C Max. process Temp.(Tp): T4; 120°C, T5; 100°C, T6; 85°C	PF22
	KOSHA Intrinsically safe Approval *1*2*3*4 Applicable Standard: Notice of Ministry of Labor No. 2010-36, EN 60079-0:2009, EN 60079-11:2012 Ex ia IIC T4 Ambient Temp.: -50 to 60°C Maximum Process Temp.: 120°C Electrical data: Ui=30 V, Ii=200 mA, Pi=0.9 W, Ci=27.6 nF, Li=0 μH	PS21

Item	Description	Code
INMETRO	INMETRO Flameproof Approval <sup>*1*2*5</sup> Applicable Standard: ABNT NBR IEC 60079-0:2013, ABNT NBR IEC 60079-1:2009 Ex d IIC T6...T4 Gb Amb. Temp. (Tamb): T4; -50 to 75°C (-58 to 167°F), T5; -50 to 80°C (-58 to 176°F), T6; -50 to 75°C (-58 to 167°F) Process Temp.(Tp): T4; -50 to 120°C (-58 to 248°F), T5; -50 to 100°C (-58 to 212°F), T6; -50 to 85°C (-58 to 185°F)	UF1
	INMETRO Intrinsically safe Approval <sup>*1*2*3*4</sup> Applicable Standard: ABNT NBR IEC 60079-0;2013, ABNT NBR IEC 60079-11;2013, ABNT NBR IEC 60079-26;2008 Ex ia IIC T4 Ga Ambient Temp.: -50 to 60°C (-58 to 140°F) Max Process Temp.(Tp): 120°C (248°F) Electrical data: Ui=30 V, Ii=200 mA, Pi=0.9 W, Ci=27.6 nF, Li=0 μH	US1

- \*1: Applicable for electrical connection code 2, 4, 7, 9, C, and D.
- \*2: Applicable for output signal code D, E, and J (E is only for EJX-A series).
- \*3: Not applicable for option code /AL (/AL is only for EJX-A series).
- \*4: Not applicable for EJX910A and EJX930A.
- \*5: Applicable for output signal code F and G.
- \*6: Applicable for output signal code P and S.

### ■ Marine Certificate Type

Item	Description	Code
Marine Certificate	American Bureau of Shipping Type Approval <sup>*1*3</sup> Certificate No.: 14-YO1127376-PDA	WCA
	Bureau Veritas Type Approval <sup>*1*3</sup> Certificate No.: 42655/A0 BV	WCB
	Det Norske Veritas Type Approval <sup>*1*3</sup> Certificate No.: A-13669	WCD
	Lloyd's Register of Shipping Type Approval <sup>*1*2*3</sup> Certificate No.: 10/10003(E1)	WCL
	Nippon Kaiji Kyokai (NK) Type Approval <sup>*1*3</sup> Certificate No.: TA16062M	WCN

- \*1: Applicable for output signal code D, E, and J (E is only for EJX-A series).
- \*2: Not applicable for measurement range 70 MPa (EJX6□0A D range and EJA5□0E /HG).
- \*3: Applicable only for process connection code 0, 1, 2, 3, 4, 5, 6, 7, 8, 9 or A, for those models which have a definition of "process connection" in their suffix code structure.  
Not applicable for a diaphragm seal system (EJXC40A, EJXC50A, EJAC50E, EJXC80A or EJAC80E)