

Exapilot - Application Capacity -

Item		Exapilot Basic				
		Standard	Professional	Office	For HIS	
Installation	No. of installation	1/PC				
	Installed destination PC	HIS	x(*1)	xx(*2)	x	x(*1)
		Exaopc-installed PC or general-purpose PC	x			-
Procedure Capacity and Restrictions	No. of built main procedures	5	20	5		
	No. of procedure concurrently executable	1	4	1		
	No. of Exapilot client (*3)	2	8	2		
	Max. No. of unit procedures	No. of unit procedures	10000/ main procedure		1000/ main procedure	
		No. of unit procedures	1000/ subprocedure			
		No. of unit procedure subprocedure	300/ main procedure			
		No. of unit procedure modules	1000/ main procedure			
No. of registered procedure modules		1000/PC				
DCS Communication	Data read from DCS	x		-	x	
	Data write to DCS	x		-	-	

*1:The Exaopc Interface Package(for HIS) needs to be prepared separately.

*2:The client can only be installed.

*3:Total number of Operation windows and Builder windows that can be connected at the same time to the procedure server.