

General Specifications

EJX Series
FOUNDATION Fieldbus™
Communication



GS 01C25T02-01E

FOUNDATION fieldbus is the digital communication line for the field instruments, whose signal is internationally standardized by Fieldbus Foundation.

The Fieldbus bi-directional digital communication performance makes possible for the field instruments and the control devices to be a complete on-line system, superseding the existing analog transmission lines. EJX series differential pressure transmitters can also measure and transmit the static pressure value. Thus, based on FOUNDATION fieldbus specifications, EJX Fieldbus models offer more flexible instrumentation through a higher level communication capability and propose the cost reduction by multi-drop wirings with less cables.



■ FEATURES

- Interoperability
FOUNDATION fieldbus specifications grant the interoperability of the field instruments without preparing designated softwares for the instrument.
- Multi-sensing function
EJX110A Fieldbus model, for example, has three independent AI function blocks for differential pressure and static pressure.
- Function blocks
Arithmetic (AR), Integrator (IT), Signal Characterizer (SC), and Input Selector (IS) function blocks are available as standard function besides three AI function blocks. PID function block is also supported as an option.
- Multi-signal display (Applicable when digital indicator is specified)
Up to four I/O signals can be alternatively displayed on the digital indicator. The block tags, the parameter names, the process units and the statuses are also displayed in order to show what the displayed signals are.
- Link master function
EJX Fieldbus models support the Link Master function. This function enables backup of network manager and local control only by field devices.
- Alarm function
EJX Fieldbus models securely support various alarm functions, such as high/low alarm, notice of block error, etc. based on FOUNDATION fieldbus specifications.
- Self-diagnostic function
The reliable self-diagnostic function detects the measuring range failure, the temperature-static pressure failure, and the hardware failure, such as pressure sensor, temperature sensor or amplifier assembly, etc.
- Advanced diagnostic function (option)
 - Impulse line blockage detection
Multi-sensing technology enables intelligent transducer block to calculate and detect impulse line abnormality particularly which side of impulse line is plugged.
 - Heat trace monitoring
The change of the flange temperature calculated by using the two temperature sensors built in the EJX enables to detect the heat trace breakage or the abnormal temperature due to the failure.
- Software download function(option)
Software download function permits to update EJX software via a FOUNDATION fieldbus. Typical use of this function is to add new features such as function blocks and diagnostics to existing devices.

STANDARD SPECIFICATIONS

For items other than those described below, refer to each General Specification sheet.

Applicable Model:

All DPharp EJX-A series, except for EJX910A Multivariable Transmitter.
For EJX910A Fieldbus communication type, refer to GS 01C25R01-01E.

Output:

Digital communication signal based on FOUNDATION fieldbus protocol.

Supply Voltage:

9 to 32 V DC for general use, flameproof type, Type n, or nonincendive.
9 to 24 V DC for intrinsically safe type Entity model
9 to 17.5 V DC for intrinsically safe type FISCO model

Communication Requirements:

Supply Voltage: 9 to 32 V DC
Current Draw:
Steady state: 15 mA (max)
Software download state: 24 mA (max)

Response Time (for Primary Value)

L capsule: 185 msec
M, H, A, B, C, D capsule: 150 msec
When amplifier damping is set to zero, and including dead time.

Update Period:

Differential Pressure: 100 msec
Static Pressure: 100 msec
Capsule Temperature: 1 sec
Amplifier Temperature: 1 sec

Integral Indicator (LCD display)

5-digit Numerical Display, 6-digit Unit Display and Bar graph. The indicator is configurable to display one or up to four of the I/O signals periodically.

Functional Specifications:

Functional specifications for Fieldbus communication conform to the standard specifications (H1) of FOUNDATION fieldbus.

Function Block:

Block name	Number	Execution time	Note
AI	3	30 mS	For differential pressure, static pressure and temperature
SC	1	30 mS	An output of Signal Characterizer block is a non-linear function of the respective input. The function is determined by a table
IT	1	30 mS	Integrator block integrates a variable as a function of the time or accumulates the counts
IS	1	30 mS	Input Selector block provides selection of up to eight inputs and generate an output based on the configured action
AR	1	30 mS	Arithmetic block permits simple use of popular measurement math functions
PID	1	45 mS	Applicable when LC1 option is specified

T01.EPS

LM Function:

LM function is supported.

MODEL AND SUFFIX CODE

EJX□□□(□)-F□□□□-□□□□□/□

□ Output signal ... Digital communication (FOUNDATION Fieldbus protocol)

OPTIONAL SPECIFICATIONS

For items other than those described below, refer to each General Specification sheet.

Item	Description	Code
PID function	PID control function	LC1
Data configuration at factory *1	Software damping	CC
Software download function	Based on FOUNDATION Fieldbus Specification(FF-883) Download class: Class1	EE
Advanced diagnostics *4	Multi-sensing process monitoring • Impulse line blockage detection *2 • Heat trace monitoring *3	DG1

T03.EPS

*1: Also see 'Ordering Information'

*2: The change of pressure fluctuation is monitored and then detects the impulse line blockage. See TI 01C25A31-01E for detailed technical information required for using this function. The function of the blockage detection for both pressure sides is applicable for model EJX110A, EJX118A, and EJX130A.

*3: Applicable for model EJX110A, EJX120A, EJX130A, EJX430A, EJX440A, EJX510A, and EJX530A

*4: This option code must be specified with option code EE.

OPTIONAL SPECIFICATIONS (For Explosion Protected type)

Item	Description	Code
Factory Mutual (FM)	FM Explosionproof Approval *1 Applicable Standard: FM3600, FM3615, FM3810, ANSI/NEMA 250 Explosionproof for Class I, Division 1, Groups B, C and D, Dust-ignitionproof for Class II/III, Division 1, Groups E, F and G, in Hazardous locations, indoors and outdoors (NEMA 4X) Temperature class: T6, Amb. Temp.: -40 to 60°C (-40 to 140°F)	FF1
	FM Intrinsically Safe and Nonincendive Approval *1 Applicable Standard: FM3600, FM3610, FM3611, FM3810, ANSI/NEMA 250, IEC60079-27 Intrinsically Safe for Class I,II, & III, Division 1, Groups A,B,C,D,E,F & G, Entity, FISCO. Class I, Zone 0, AEx ia IIC, Enclosure: "NEMA 4X", Temp. Class: T4, Amb. Temp.: -40 to 60°C (-40 to 140°F). Intrinsically Apparatus Parameters : [FISCO (IIC)] Ui=17.5 V, li=380 mA, Pi=5.32 W, Ci=1.76 nF, Li=0 ∞H [FISCO (IIB)] Ui=17.5 V, li=460 mA, Pi=5.32 W, Ci=1.76 nF, Li=0 ∞H [Entity] Ui=24 V, li=250 mA, Pi=1.2 W, Ci=1.76 nF, Li=0 ∞H Nonincendive for Class I, Division 2, Groups A, B, C and D, NIFW, FNICO Class I, Zone 2, Group IIC, NIFW, FNICO Class II, Division 2, Groups F&G, and Class III, Division 1 Enclosure: "NEMA 4X", Temp. Class: T4, Amb. Temp.: -40 to 60°C (-40 to 140°F) Nonincendive Apparatus Parameters : Vmax.= 32 V, Ci = 1.76 nF, Li = 0	FS15
CENELEC ATEX	CENELEC ATEX (KEMA) Flameproof Approval *1 Applicable Standard: EN 60079-0, EN 60079-1, EN 61241-0, EN 61241-1 Certificate: KEMA 07ATEX0109 II 2G, 2D Exd IIC T4, T5, T6 Ex tD A21 IP6X T85, T100, T120 Degree of protection : IP66 and IP67 Amb. Temp. (Tamb) for gas-proof : T4 ; -50 to 75°C (-58 to 167°F), T5; -50 to 80°C (-58 to 176°F), T6; -50 to 75°C (-58 to 167°F) Max. process Temp.(Tp): T4; 120°C (248°F), T5; 100°C (212°F), T6; 85°C (185°F) Max. surface Temp. for dust-proof : T85°C (Tamb: -40 to 40°C, Tp:85°C), T100°C (Tamb: -40 to 60°C, Tp:100°C), T120°C (Tamb: -40 to 80°C, Tp:120°C)	KF21
	CENELEC ATEX (KEMA) Intrinsically safe Approval *1 Certificate: KEMA 04ATEX1116X Applicable standards: EN 50014, EN 50020, EN 50284, EN 50281-1-1 II 1GD EEx ia IIB/IIC T4 Amb. Temp. : -40 to 60°C (-40 to 140°F) Max. Process Temp. (Tp) : 120°C (248°F) Max. Surface Temp. for dust-proof: T85°C (Tp:80°C), T100°C (Tp:100°C), T120°C (Tp:120°C) Enclosure : IP66 and IP67 [FISCO (IIC)] Ui=17.5V, li=380mA, Pi=5.32W, Ci=1.76nF, Li=0∞H [FISCO (IIB)] Ui=17.5V, li=460mA, Pi=5.32W, Ci=1.76nF, Li=0∞H [Entity] Ui=24V, li=250mA, Pi=1.2W, Ci=1.76nF, Li=0∞H	KS25
	CENELEC ATEX Type n Approval *1 Applicable standards: EN 50021, EN 60529 EEx nL IIC T4 Amb. Temp. : -40 to 60°C (-40 to 140°F), Enclosure : IP66 and IP67 Ui=32V, Ci=1.76nF, Li=0	KN25
Canadian Standards Association (CSA)	CSA Explosionproof Approval *1 Certificate: 1966237 Applicable Standard: C22.2 No.0, C22.2 No.0.4, C22.2 No.0.5, C22.2 No.25, C22.2 No.30, C22.2 No.94, C22.2 No.60079-0, C22.2 No.60079-1, C22.2 No.61010-1-01 Explosion-proof for Class I, Groups B, C and D. Dustignition-proof for Class II/III, Groups E, F and G. When installed in Division 2, "SEAL NOT REQUIRED" Enclosure: TYPE 4X, Temp. Code: T6...T4 Ex d IIC T6...T4 Enclosure: IP66 and IP67 Max.Process Temp.: T4;120°C (248°F), T5;100°C (212 °F), T6; 85°C (185°F) Amb.Temp.: -50 to 75°C (-58 to 167°F) for T4, -50 to 80°C(-58 to 176°F) for T5, -50 to 75°C (-58 to 167°F) for T6	CF1

T02.EPS

Item	Description	Code
IECEX Scheme *2	IECEx Flameproof Approval *1 Applicable Standard: IEC 60079-0:2004, IEC60079-1:2003 Certificate: IECEx CSA 07.0008 Flameproof for Zone 1, Ex d IIC T6...T4 Enclosure: IP66 and IP67 Max.Process Temp.: T4;120°C(248°F), T5;100°C(212°F), T6; 85°C(185°F) Amb.Temp.: -50 to 75°C(-58 to 167°F) for T4, -50 to 80°C(-58 to 176°F) for T5, -50 to 75°C(-58 to 167°F) for T6	SF2
	IECEx Intrinsically safe and type n Approval *1 No. IECEx CSA 05.0012 Applicable Standard: IEC 60079-0:2000, IEC 60079-11:1999, IEC 60079-15:2001 Ex ia IIC/IIB T4, Ex nL IIC T4 Ambient Temperature : -40 to 60°C Max. Process Temp.: 120°C Enclosure: IP66 and IP67 Intrinsically safe ratings: [Entity] Ui = 24 V, li= 250 mA, Pi = 1.2 W, Ci = 1.76 nF, Li = 0 ∞H [FISCO IIC] Ui = 17.5 V, li = 380 mA, Pi = 5.32 W, Ci = 1.76 nF, Li = 0 ∞H [FISCO IIB] Ui = 17.5 V, li = 460 mA, Pi = 5.32 W, Ci = 1.76 nF, Li = 0 ∞H Type "n" ratings : Ui = 32 V, Ci = 1.76 nF, Li = 0 ∞H	SS25

T02_02.EPS

Contact Yokogawa representative for the codes indicated as '-'.
 *1: Applicable for Electrical connection code 2, 4, 7, 9, C and D .
 *2: Applicable only for Australia and New Zealand area.

<Ordering Information>

- Specify the following when ordering
1. Model, suffix codes, and optional codes
 2. Calibration range and unit (XD_SCALE of AI1);
 - 1) Calibration range can be specified with range value specifications up to 5 digits (excluding any decimal point) for low or high range limits within the range of -32000 to 32000.
 - 2) Specify only one unit from the table, 'Factory Setting'.
 3. Output mode (L_TYPE of AI1);

Select 'Direct', 'Indirect Linear' or 'Indirect Sqrt'.
 4. Output scale and unit (OUT_SCALE of AI1);

When digital indicator is required, the scale range can be specified with range limit specifications up to 5 digits (excluding any decimal point) for low or high range limits within the range of -32000 to 32000. Unit display consists of 6-digit, therefore, if the specified scaling unit excluding '/' is longer than 6-characters, the first 6 characters will be displayed on the unit display. When L_TYPE is Direct, these setting does not affect the output of the AI block
 5. Tag Number;

Specify software tag (up to 30 letters) to be written on the amplifier memory and Tag number (up to 18 letters) to be engraved on the tag plate separately.
 6. Node Address
 7. Operation Functional Class

Select 'BASIC' or 'LINK MASTER'

[When /CC option is specified]

8. Software damping (PRIMARY_VALVE_FTIME of TB);

Specify software damping : 0.00 to 100.00 (sec)

Example; When 50 to 1000 mmH₂O for calibration range and 0 to 100% output range is required, specify the values as follows:

Calibration range:		
	Higher value	1000
	Lower value	50
Calibration unit:		mmH ₂ O
Output range:		
	Higher value	100
	Lower value	0
Unit of output range:		%
Output mode:		Indirect Linear

Explanation of Fieldbus parameters:

- (1) XD_SCALE: Set the input value from Transducer block (input range of sensor) which corresponds to 0% value and 100% value of the calculation in the AI function block. In the case of EJJ series, the value set as calibration range should be entered to this parameter.
- (2) OUT_SCALE: Output scaling parameter. Set the output value which corresponds to 0% value and 100% value of the calculation in the AI function block. In the case of EJJseries, the value set as output scale should be entered to this parameter. When integral indicator is required, this output is shown on LCD.
- (3) L_TYPE: Determines if the values passed by the transducer block to the AI block may be used directly (Direct) or if the value is in different units and must be converted linearly (Indirect Linear) or with square root (Indirect Sqrt), using the input range defined by XD_SCALE and the associated output range (OUT_SCALE).

< Related Instruments >

The customer should prepare instrument maintenance tool, terminator, fieldbus power supply etc.

<Reference>

FOUNDATION; Trademark of Fieldbus Foundation.

< Factory Setting >

Tag Number (Tag plate)	As specified in order	
Software Tag (PD_TAG)	'PT2001' unless otherwise both Tag Number and Software Tag specified in order	
Node Address	'0xF5' unless otherwise specified in order	
Operation Functional Class	'BASIC' or as specified	
Primary value *1	Output Mode (L_TYPE)	'Direct' unless otherwise specified in order
	Calibration Range (XD_SCALE) Lower/Higher Range Value	As specified in order
	Calibration Range Unit	Selected from mmH ₂ O, mmH ₂ O(68°F), mmHg, Pa, hPa, kPa, MPa, mbar, bar, gf/cm ² , kgf/cm ² , inH ₂ O, inH ₂ O(68°F), inHg, ftH ₂ O, ftH ₂ O(68°F) or psi. (Only one unit can be specified)
	Output Scale (OUT_SCALE) Lower/Higher Range Value	'0 to 100%' unless otherwise specified.
	Software Damping *2	'2 seconds' or as specified in order
Static pressur display range	'0 to 25 MPa' for M and H capsule and '0 to 16 MPa' for L capsule, absolute value. Measuring high pressure side.	

T04.EPS

*1: Primary means differential pressure in case of differential presser transmitters and pressure in case of pressure transmitters.
 *2: To specify this item, /CC option is required.