


## Dissolved-oxygen Metering System DO30G - NN - 50 - □ □ - PN Dissolved - oxygen Sensor

Unit : mm

- Dissolved-oxygen sensor with pin terminals



Model and Suffix Codes	L	Weight (kg)
DO30G - NN - 50 - 03 - PN	3 000	Approx. 0.6
DO30G - NN - 50 - 05 - PN	5 000	Approx. 0.8
DO30G - NN - 50 - 10 - PN	10 000	Approx. 1.4
DO30G - NN - 50 - 15 - PN	15 000	Approx. 2.0
DO30G - NN - 50 - 20 - PN	20 000	Approx. 2.6

Unless otherwise specified, differences in the dimensions are specified as : General tolerance= $\pm$ (Criteria of tolerance class IT18 in JIS B0401)/2.