


PH97 SENSOR CABLE



PH87J-BOX
TERMINAL

| | |
|---|-------------------|
| 5 | CENTER WHITE COAX |
| 3 | CENTER BROWN COAX |
| 1 | RED |
| 2 | BLUE |
| 4 | OVERALL SHIELD |


WF10 CABLE
LENGTH VARIES

| | |
|----------------|----|
| CENTER WHITE | 15 |
| SHIELD WHITE | 16 |
| CENTER BROWN | 13 |
| SHIELD BROWN | 17 |
| RED | 11 |
| BLUE | 12 |
| OVERALL SHIELD | 14 |

EXA
ANALYZER
TERMINAL

| |
|----|
| 15 |
| 16 |
| 13 |
| 17 |
| 11 |
| 12 |
| 14 |

NOTE:
MINIMUM CLEARANCE
FOR SENSOR REMOVAL
29.40 [746.8]



PH87-07 RETRACTABLE pH ASSEMBLY
WITH 1 1/4 IN. 316SS BALL VALVE

UNITS:
IN [MM]


YOKOGAWA

2 DART ROAD

NEWNAN, GEORGIA 30265

PH97 SENSOR CABLE

COAX




pH/ORP CLEAR
REF BLACK
TC RED
TC BLACK
SOLN GND GREEN

PH87J-BOX
TERMINAL


| | |
|---|-------------------|
| 5 | CENTER WHITE COAX |
| 3 | CENTER BROWN COAX |
| 1 | RED |
| 2 | BLUE |
| 4 | OVERALL SHIELD |

WF10 CABLE
LENGTH VARIES



| | |
|----|----------------|
| 15 | CENTER WHITE |
| 16 | SHIELD WHITE |
| 13 | CENTER BROWN |
| 17 | SHIELD BROWN |
| 11 | RED |
| 12 | BLUE |
| 14 | OVERALL SHIELD |

EXA
ANALYZER
TERMINAL



PH87-21 RETRACTABLE pH ASSEMBLY
WITHOUT BALL VALVE

UNITS:
IN [MM]

YOKOGAWA ◆

2 DART ROAD

NEWNAN, GEORGIA 30265