



INTERNAL WIRING
INSTALLED AT FACTORY

- CERTIFIED DRAWING
- *1 THE PROTECTIVE GROUNDING FOR THE CONVERTER SHALL BE CONNECTED EITHER THE PROTECTIVE GROUND TERMINAL IN THE EQUIPMENT OR THE GROUND TERMINAL ON THE CASE. STANDARD REGARDING GROUNDING, JIS D TYPE (CLASS 3 GROUNDING) GROUND RESISTANCE 100ΩMS OR LESS.
 - *2 SUPPLY VOLTAGE FOR THE IAC24S 24VDC AND IS PROVIDED BY THIRAKOG.

P.O. NUMBER
TAG #46

MODEL	ZR40G	TYPE	SEPARATE TYPE
PROBE	ZR22-O2	HEATER	10.0W
WIRING	WIRING SCHEMATIC FOR ZR40G & ZR22-O2 SYSTEM		
NOTE	24VDC IS SUPPLIED FOR IAC24 BY ZR40G		
DATE	2008.03		
REVISION	1		
YOKOGAWA		ANALYTICAL INSTRUMENTS	
YOKOGAWA ELECTRIC CO., LTD.		1-2-3, SHIBUYA-KU, TOKYO 100-8302, JAPAN	
TEL: +81 (0)3 3457 3451		FAX: +81 (0)3 3457 3452	
E-MAIL: info@yokogawa.com		WWW: www.yokogawa.com	