



**SCOPECORDER**

**Complete measurements  
Complete portability**

**DL350  
ScopeCorder**

**Precision Making**

Bulletin DL350-01EN



A stringent measurement condition requires a high performance and flexible solution. This is the design philosophy of the DL350 ScopeCorder. With the ability to use the same 17 types of plug-in module as other ScopeCorders, the battery portable DL350 is easier to carry and easier to use in confined spaces.

Offering channel counts up to 8 analog and 16 digital, sample rates up to 100 MS/s, Isolation up to 1 KV and resolution up to 16-bit, the range of modules enables the DL350 to be configured for a multitude of long and short term measurement applications.

Rechargeable battery operation can be used for testing in remote areas or as a UPS when combined with mains power.

#### The DL350 delivers:

**Portability** – The light weight, battery operation and compact size makes the DL350 the all-round instrument-of-choice in the vehicle and in the field.

**Functionality** – The built-in memory provides long term recording and transient capture. An SD card provides long term storage. Advanced triggering ensures that the data is captured during the most critical of tests.

**Operability** – Use it like a recorder or an oscilloscope. The touch screen and choice of operating modes mean that the DL350 is as useful for simple maintenance tasks as it is for advanced measurement and analysis needs.



Maximum 8-ch high-speed isolated recording in a battery-operated compact chassis

- A4-sized compact chassis
- Simultaneous isolated inputs maximum 8-ch (1 MS/s) or 4-ch (100 MS/s)  
Scanning inputs maximum 32-ch (10 kS/s) or 16 channels (20 kS/s)
- AC/DC/Battery operated



Superior noise and vibration-proof Flexible recording in a single portable tool

- Choose from 17 types of input module, which are compatible with other ScopeCorders.
- Vibration-resistant design
- Superior immunity
- Secure reliable data recording in harsh environment


# ScopeCorder DL350

 UP TO  
**100 Mpoints**  
/Module

 UP TO  
**20 Gpoints**  
/Module

High-speed and long-term recording using large memory and direct recording onto an SD card

- Up to 100 Mpoints per module memory
- Up to 50 days continuous recording onto SD card



Ease of use in the field

- Intuitive operation using 8.4-inch touch screen
- A choice of two operating modes provides greater flexibility
- “DL350 assistant software” helps to configure settings and to back-up data on-the-spot



# More than a test tool

The DL350 ScopeCorder combines in one compact instrument all the measurement and recording capabilities you need when you are away from your office or lab. High-speed signals or long-term recording, ‘quick and simple’ or sophisticated operation, the DL350 provides the flexibility you need when you need it.

## Complete self-contained signal conditioning

Whether it is straightforward high precision voltage measurements or a blend of signals coming from such things as current probes, temperature sensors, strain gauges, accelerometers and serial buses, the DL350 can handle them all without extra boxes or cables.



This extraordinary input capability is achieved by providing 2 slots, which can be populated with any of 17 different types of user swappable input modules. This means, for example, that user-swappable 4 isolated 16-bit voltage inputs can be measured at 1 MS/s, alongside 16 temperatures or 2 separate CAN/CAN FD or LIN buses each containing 60 signals. Swap a module and measure at 100 MS/s with 12-bit and 1 kV of isolation. Meanwhile there are 16 built-in logic inputs; swap in a digital input module to add even more. Make AC measurements like a DMM with an RMS module in real-time or use a math channel after the recording is finished.



## Examples of complex measurements

Field	Application purpose	Measurement item		User advantages
		Slot 1	Slot 2	
EV (electric vehicle) 	Evaluation of battery voltage fluctuation while driving	Battery voltage	CAN/CAN FD communication data	Small size, battery drive, synchronization with GPS* position and time data
Power tool 	Evaluation of practical behavior	Battery voltage, motor rotation pulse	Tool vibration	Small size, battery drive, complex measurement of voltage and vibration
Field device 	Maintenance of ultrasonic-type vortex flow meter	Sensor receiving wave, receiving pulse	Gate signal	Small size, 2-way power source, long-term monitoring with long memory
Factory/plant 	Power quality monitoring	AC power, voltage, current	Auxiliary power source monitor	Small, portable, window trigger (instantaneous power failure, sag detection)
Steel making Paper making 	Rolling process monitoring	Thickness gauge monitor	Temperature	High noise immunity, external clock (roller) synchronization


\*The GPS unit can only be supplied to countries where it is not prohibited by local radio laws.

## Use it like a data acquisition system or a long memory oscilloscope

Up to 5 Gpoints of data per module can be recorded directly to an SD card. This means that the DL350 can be used for continuous recording for up to 50 days. For high speed signals, up to 100 M points per module of internal memory is available to capture fast transients. This is up to 10000 times more than other portable oscilloscopes or test tools and thus signals can be captured with higher sample rates or for much longer periods.

## Accurate measurement of fast-switching waveforms

Unique amongst portable measuring instruments, there is a high-resolution high-speed sampling module available for the DL350. This provides individually isolated 12-bit, 100 MS/s inputs, which can precisely measure and record transient waveforms superimposed on slower signals. For example, transients occurring on inverter outputs, or the edges of control signals, which are beyond the reach of traditional handheld test tools.



Gate signal waveforms of inverter (20 kHz)  
The picture on the left shows a waveforms measured with 100 MS/s (by 720211 module) that is sufficiently high sample rate to accurately reconstruct the signal, which will result in more accurate measurements than the one on the right that measured with 1 MS/s

### Measurement examples to built-in memory

#### Scope mode

Sample Rate	For 1 ch <sup>1</sup>	For 4 ch <sup>2</sup>	For 8 ch <sup>3</sup>
100 MS/s	1 s	0.5 s	—
10 MS/s	10 s	5 s	—
1 MS/s	1 min. 40 s	50 s	20 s
100 kS/s	10 min.	5 min.	3 min. 20 s
10 kS/s	2 hours	1 hour	40 min.
1 kS/s	20 hours	10 hours	5 hours
100 S/s	10 days	5 days	60 hours
10 S/s	50 days	50 days	20 days
5 S/s	50 days	50 days	50 days

#### Recorder mode

Sampling interval	For 1 ch <sup>1</sup>	For 4 ch <sup>2</sup>	For 8 ch <sup>3</sup>
—	—	—	—
1 μs	20 s	20 s	10 s
10 μs	3 min. 20 s	3 min. 20 s	1 min. 40 s
100 μs	40 min.	40 min.	10 min.
1 ms	5 hours	5 hours	2 hours
10 ms	60 hours	60 hours	20 hours
100 ms	20 days	20 days	10 days
200 ms	20 days	20 days	20 days

### Measurement examples to SD memory card<sup>4</sup>

#### Scope mode

Sample Rate	For 1 ch <sup>1</sup>	For 4 ch <sup>2</sup>	For 8 ch <sup>3</sup>
1 MS/s	5 hours	—	—
100 kS/s	50 hours	20 hours	10 hours
10 kS/s	20 days	10 days	120 hours
1 kS/s	50 days	50 days	50 days
100 S/s	50 days	50 days	50 days
10 S/s	50 days	50 days	50 days
5 S/s	50 days	50 days	50 days

#### Recorder mode

Sampling interval	For 1 ch <sup>1</sup>	For 4 ch <sup>2</sup>	For 8 ch <sup>3</sup>
1 μs	1 hour	—	—
10 μs	10 hours	10 hours	5 hours
100 μs	120 hours	120 hours	50 hours
1 ms	50 days	50 days	20 days
10 ms	50 days	50 days	50 days
100 ms	50 days	50 days	50 days
200 ms	50 days	50 days	50 days

\*1: When using one module of 720211 \*2: When using two modules of 720211 \*3: When using two modules of 720254 \*4: The firmware version 1.20 or later is required.


# Comprehensive testing made easy

## Full recording flexibility

For users who are more familiar with chart recorders than with long memory oscilloscopes, the DL350 offers a choice of operating modes. Recorder mode is suitable for long-term continuous recording for a specific duration and where the sampling interval is specified. A setup wizard can be used in this mode to quickly guide the operator through the entire setup process.



Scope mode enables the DL350 to be used just like an oscilloscope with all the associated benefits, like comprehensive triggering and flexible memory use. Using the history memory enables up to 1000 separate triggered acquisitions to be captured to the internal memory and viewed afterwards. Thus the causes and effects of abnormalities can be carefully analyzed as easily as paging through a photo album.



## Intuitive operation

An 8.4 inch resistive touch screen has been adopted in order to deliver superior noise free performance. In environments with the highest levels of electrical noise such as motors and inverters, measurement precision is maintained whilst enabling the unit to be operated by using (gloved) fingers or stylus.



Even when the backlight is switched off and the touch screen is inactive the user still has access to the START/STOP, manual trigger and data saving keys. For users unfamiliar with state-of-the-art measuring instruments, there is also help at hand via the built-in digital manual.

If the amplitude or period of an input signal is unknown, press "Auto Setup" and the vertical and horizontal axes are automatically set. The display of channels with no input signal is automatically turned off.\*




\*Auto Setup doesn't work for some modules.

### A wealth of triggers for fault finding


The user has a choice of a simple level trigger or can use enhanced triggers such things as pulse width, waveform period and across multiple channels. For example, the wave window trigger is ideal for AC power line monitoring which enables voltage sags, surges, spikes, phase shifts or drop outs to be easily captured (available for 40 to 1000 Hz waveforms).

Leave a DL350 unattended and automatically save the waveform to a file, or send a notification email, if and when it triggers.



### External sampling clock and triggers

The DL350 is first and foremost a field tool however it still provides the functionality you expect in a bench instrument. The sampling clock, trigger and start/stop controls are all available as external signals, thus, for example, a rotary angle encoder or degree wheel can be used as the sample clock to analyze engine rotation and performance.




### Verify power line quality using harmonic, power or FFT analysis


The power in single and 3 phase systems can be evaluated. Additionally for fundamental waveforms of 50 or 60 Hz, up to 40 harmonic orders can be analyzed. Alternatively use the suite of FFT functions to perform full frequency analysis.



Harmonics analysis (bar graph)



Harmonics analysis (listed)




FFT analysis


# Advanced features to support in-vehicle testing

## CAN/CAN FD, LIN and SENT monitoring

Use the DL350 with /VE option and bus monitor module to decode CAN/CAN FD, LIN bus or SENT signals and display information such as engine temperature, vehicle speed and brake pedal position as trend waveforms and compare this with the analog data coming from the actual sensors. This enables automotive engineers to gain an insight into the dynamic behavior of the complete electromechanical system.





The symbol editor is a software tool that makes it possible to define which physical values from the CAN/CAN FD or LIN bus data frame will be trended as waveform data on the display of the DL350. The Symbol Editor can accept vehicle installed definition files (CAN DBC, LIN LDF)



## Position and global timing using GPS

An optional GPS unit\* enables latitude, longitude, altitude, speed and motion direction data to be synchronized with the waveform data, perfect for drive testing, mobile testing, or distributed field recordings.

\*The GPS unit can only be supplied to countries where it is not prohibited by local radio laws.



DIAdem is the trademark of National Instruments Ireland Resources Limited.

## Mains, DC or rechargeable battery power

The built-in rechargeable battery provides 3 hours of continuous operation for mobile measurements or can serve as a backup power supply if the main AC/DC power is disconnected. This makes the DL350 a highly reliable ScopeCorder for tests which are difficult or expensive to repeat.



## Operates in freezing temperatures

Even when used with the rechargeable battery, the DL350 will operate in temperatures from 0 to 45 degrees. The DL350 brings high-quality laboratory measurements into the harsh environments of the field.



## Vibration resistant

Instruments used for in-vehicle driving tests or field maintenance must be able to make reliable measurements. The DL350 has an aluminum inner frame and an external rubber bumper and conforms to the Japanese JIS D1601 standard for resisting in-vehicle shock and vibration.



Rubber bumper



# Technology Story


Input modules used in the DL350 ScopeCorder are compatible with the DL950 ScopeCorders, and the SL1000. The DL350 inherits the technological developments of more than 30 years of commitment to the measurement needs of electromechanical systems.

## isoPRO – pioneering measurement technology



Input modules are powered by YOKOGAWA's isoPRO technology, which offers industry-leading isolation performance at the highest speeds. isoPRO core technology, designed with energy-saving applications in mind, delivers the performance needed to develop high-efficiency inverters that operate at high voltages, large currents and high frequency.

The use of optical fibers enables the achievement of high speed data transmission and high voltage isolation.



## Higher voltage registration and better CMRR



### 720268 High Voltage Input Module

The new high-Voltage, high-resolution, 1 MS/s 16 bit Isolation Module (model 720268), which is also capable of direct RMS measurements, has an improved sample rate (1 MS/s) and an improved maximum input voltage (1000 Vrms).

Normally, to realize high insulation performance in a small package, it is necessary to raise the input impedance and lower the voltage of the internal circuit. However the increase in input impedance causes a reduction in the common-mode rejection ratio (CMRR) and measurement accuracy.

Thanks to the new digital isolator in this module, high voltage input signals can be acquired without an increase in size. High insulation performance is maintained without compromising the CMRR.



# Flexible operation



- |  |  |
|--|--|
| <p><b>1 START/STOP key</b><br/>LED indicates the DL350 measuring status.</p> <p><b>2 TRIGGER key</b><br/>Used for triggering the DL350 manually</p> <p><b>3 SAVE key</b><br/>A pre-programmable button that saves data to SD card or network storage</p> <p><b>4 Power switch</b></p> <p><b>5 8.4-inch touch screen</b></p> <p><b>6 Input module slots (2 slots)</b></p> <p><b>7 Logic input terminals</b></p> | <p><b>8 GPS* input terminal</b></p> <p><b>9 EXT I/O</b><br/>Multifunctional port used for external start/stop input, trigger I/O, external clock input and other functions</p> <p><b>10 SD memory card slot</b></p> <p><b>11 USB ports for peripherals and storage devices</b></p> <p><b>12 Ethernet (100BASE-TX/10BASE-T)</b></p> <p><b>13 USB port (PC)</b></p> <p><b>14 Battery pack (/EB option)</b></p> |
|--|--|

\*The GPS unit can only be supplied to countries where it is not prohibited by local radio laws.

# The application solver

Using different modules and accessories, the DL350 ScopeCorder addresses the complex measurement and analysis needs of widely diverse applications in the field.


## Electric vehicle inverter voltage evaluation

The voltage fluctuations of the input and output of the inverter can be measured alongside the trends of speed, acceleration and braking from the data on the CAN/CAN FD bus.

Up to 20-hours of continuous data can be directly recorded to the SD card with sample rates up to 100 kS/s.

The optional rechargeable battery pack enables the DL350 to be continuously operated without burdening the in-vehicle power supply.

The optional GPS unit\* adds coordinate information to the recording data to enable the measurements to be correlated with the location of the vehicle in a drive test.



Recommended modules		Recommended accessory
High-speed isolated module (100 MS/s)		GPS unit* 
	CAN FD/LIN monitor module (/VE option required) 	

\*The GPS unit can only be supplied to countries where it is not prohibited by local radio laws.


## Remote monitoring of power lines in plants and factories

By connecting to an IoT gateway device\*, remote monitoring and operation via wireless connection is available without an Internet connection.

By using a wave window trigger, voltage sags, surges, spikes, and dropouts can be detected and captured.

The DL350 can save a waveform or send an email when a trigger happens, which is useful when the DL350 is not being monitored.

\*The IoT gateway in the figure is a product of SECOMEA.




Recommended modules	Recommended accessory	Recommended functions
High-voltage isolated module (1 kVrms) 	Xwirepuller 	Wave window trigger, Action on trigger

## Industrial robot maintenance

It is possible to monitor and record the control signals to the servomotors and their speed and torque at the same time.

For condition monitoring, FFT analysis can be used on the vibration signals from accelerometers to help identify potential failures in machines or components.

Remote operation is available using the 'assistant software' or the input/output terminals making it potentially safer to use.



Recommended modules	Recommended functions
4-ch input isolated module  Acceleration/Voltage module 	FFT analysis, Remote control

# Consistent measurement results in R&D and maintenance

Traditionally different measuring instruments of various sizes and capabilities are used in the R&D lab and in the field. Since the accuracy, noise immunity and other characteristics are not the same, engineers struggle to correlate measurements.


The plug-in modules of the DL350 are common\* to those of the DL950, the higher-end ScopeCorder models. By using common\* modules for product design, validation and on-site maintenance, the high quality of the measurements is consistent.

\*With some exceptions

IF CLASS 1 LASER PRODUCT MODULE IS AVAILABLE  
 クラス1レーザーモジュール実装時  
 安裝Class 1激光模块时

**CLASS 1 LASER PRODUCT**  
 クラス1レーザー製品  
 1类激光产品  
 (EN 60825-1:2014 + A11:2021)  
 (IEC 60825-1:2007, GB 7247.1-2012)

Complies with 21 CFR 1040.10 and 1040.11 except for deviations pursuant to Laser Notice No.50, dated June 24, 2007  
 4-9-8 Myojin-cho, Hachioji-shi, Tokyo 192-8566, Japan




## CAN FD/LIN Monitor Module 720245\*



### Monitor and decode CAN FD (CAN with Flexible Data Rate)

The 720245 module is capable of extracting specified data from CAN FD serial signals as well as Classical CAN, converting them into analog values, and record their trends. It therefore strongly supports the development and evaluation of next-generation vehicles. The 720245 module allows a network intermingled with CAN and CAN FD to be monitored by automatically discriminating between these two formats.


\*Operation of 720245 requires /VE option.



### CAN FD (CAN with Flexible Data-rate) versus Classical CAN

CAN FD is a format in which the transfer rate and data length of the data field has been increased while still following a protocol common to CAN. It therefore enables data rates higher than 1 Mbit/s to be transmitted on a CAN bus and thus deliver the higher bandwidths now required by the automotive industry for in-vehicle networks.

### Input module lineup for DL350



Notes: The following modules are not available on DL350  
701250, 701251, 701255, 701267, 701281, 720210, 720212, 720256, 701260, 701280

### Module selection

Input	Model No. <sup>*1</sup>	Sample rate	Resolution	Bandwidth	Number of channels	Isolation	Maximum measurement voltage <sup>*11</sup> (DC+ACpeak)	DC accuracy	Note
Analog Voltage	720211 <sup>*9</sup>	100 MS/s	12-Bit	20 MHz	2	Isolated	1000 V <sup>2</sup> , 200 V <sup>5</sup>	±0.5%	High speed · High voltage · Isolated
	720250	10 MS/s	12-Bit	3 MHz	2	Isolated	800 V <sup>2</sup> , 200 V <sup>5</sup>	±0.5%	high noise immunity
	720254	1 MS/s	16-Bit	300 kHz	4	Isolated	600 V <sup>2</sup> , 200 V <sup>5</sup>	±0.25%	4-CH BNC input, low noise, high noise immunity
	720268	1 MS/s	16-Bit	300 kHz	2	Isolated	1000V <sup>10</sup> · <sup>12</sup>	±0.25%	with AAF, RMS, and high noise immunity
	720220	200 kS/s	16-Bit	5 kHz	16	Isolated (GND-terminal) non-isolated (CH-CH)	20 V <sup>3</sup>	±0.3%	16-CH voltage measurement (Scan-type)
Analog Voltage & Temperature	720221 <sup>*9</sup>	10 S/s	16-Bit	600 Hz	16	Isolated	20 V	±0.15% (Voltage)	16-CH voltage or temperature measurement (scan method) Thermocouple (K, E, J, T, L, U, N, R, S, B, W, KP/AuFe)
	701261	100 kS/s (Voltage), 500 S/s (Temperature)	16-Bit (Voltage), 0.1°C (Temperature)	40 kHz (Voltage), 100 Hz (Temperature)	2	Isolated	42 V	±0.25% (Voltage)	thermocouple (K, E, J, T, L, U, N, R, S, B, W, KP/AuFe)
	701262	100 kS/s (Voltage), 500 S/s (Temperature)	16-Bit (Voltage), 0.1°C (Temperature)	40 kHz (Voltage), 100 Hz (Temperature)	2	Isolated	42 V	±0.25% (Voltage)	thermocouple (K, E, J, T, L, U, N, R, S, B, W, KP/AuFe), with AAF
	701265	500 S/s (Voltage), 500 S/s (Temperature)	16-Bit (Voltage), 0.1°C (Temperature)	100 Hz	2	Isolated	42 V	±0.08 (Voltage)	thermocouple (K, E, J, T, L, U, N, R, S, B, W, KP/AuFe), high sensitivity range (0.1 mV/div)
	720266	125 S/s (Voltage), 125 S/s (Temperature)	16-Bit (Voltage), 0.1°C (Temperature)	15 Hz	2	Isolated	42 V	±0.08 (Voltage)	thermocouple (K, E, J, T, L, U, N, R, S, B, W, KP/AuFe), high sensitivity range (0.1 mV/div), and low noise (±4 µVtyp.)
Strain	701270	100 kS/s	16-Bit	20 kHz	2	Isolated	10 V	±0.5% (Strain)	Supports strain NDIS, 2, 5, 10 V built-in bridge power supply
	701271	100 kS/s	16-Bit	20 kHz	2	Isolated	10 V	±0.5% (Strain)	Supports strain DSUB, 2, 5, 10 V built-in bridge power supply, and shunt CAL
Analog Voltage, Acceleration	701275	100 kS/s	16-Bit	40 kHz	2	Isolated	42 V	±0.25% (Voltage) ±0.5% (Acceleration)	built-in anti-aliasing filter, Supports built-in amp type acceleration sensors (4 mA/22 V)
Frequency	720281	1 MS/s	16-Bit	resolution 625 ps	2	Isolated	420 V <sup>2</sup> , 42 V <sup>3</sup>	±0.1% (Frequency)	Measurement frequency of 0.01 Hz to 500 kHz, Measured parameters (frequency, rpm, period, duty, power supply frequency, distance, speed)
Logic	720230	10 MS/s	—	—	8-bit × 2 ports	non-isolated	depend on logic probe used.	—	(8-bit/port) × 2, compatible with four-type of logic probe (sold separately)
CAN/CAN FD/LIN	720245	100 kS/s	—	—	60 signals × 2 port	Isolated	10 V (CAN port) 18 V (LIN port)	—	CAN/CAN FD port × 2, CAN/CAN FD Data of maximum 32-bit allowable, LIN port × 2 CAN FD/LIN switchable on each port separately Available for DL950/VCE and DL350 /VE option. <sup>*5-7</sup>
SENT	720243	100 kS/s	—	—	11 data × 2 ports	Isolated	42 V	—	Supported protocol: SAE J2716. Available for DL950/VCE and DL350 /VE option. <sup>*5-7</sup>


\*1: Probes are not included with any modules. \*2: In combination with 700929, 702902 or 701947 probe. \*3: Direct input \*4: In combination with 10:1 probe model 701940 \*5: In combination with 701901 + 701954. \*6: Any other modules can be installed in the remaining slots. \*7: In the DL950/VCE, up to four CAN Bus Monitor Module (720240), CAN & LIN Bus Monitor Module (720241), CAN/CAN FD Monitor Module (720242), CAN FD/LIN Monitor Module (720245) or SENT Monitor Module (720243) in total can be used on a single main unit. In the DL950/VCE, for the CAN Bus Monitor Module (720240), CAN & LIN Bus Monitor Module (720241), CAN/CAN FD monitor module (720242) and CAN FD/LIN Monitor Module (720245), up to two in total can be used on a single main unit. \*8: The 16-CH Scanner Box (701953) is required for measurement. \*9: Class 1 Laser Product, IEC/EN60825-1, GB7247.1-2012 \*10: In combination with 758933 and 701954 or 701904 and 701954. \*11: See Bulletin DL950-Q2EN for voltage-axis sensitivity setting and measurement range. \*12: 1000 Vrms (1000 VDC or 1414 Vpeak maximum) However, when using with SL1000, 850V (DC + AC peak)

# Accessories and software

## Display and analysis of recorded waveforms

### IS8000 Integrated Software Platform — Advanced Software —

The IS8000 offers high-speed data acquisition in combination with the DL950. Additionally, IS8000 enables synchronous measurement with power analyzers, third-party high-speed cameras, and RAM monitors, waveform analysis, device control, and report output. Combined with the DL350, the integrated software platform loads and displays captured waveforms, exports the data to CSV/MDF format, and performs parameter measurement, statistical analysis, arithmetic, FFT, and filtering. In addition, IS8000 allows you to remotely control the DL350 and monitor waveforms on its screen via USB or Ethernet.



See Bulletin IS8000-01EN for more detail about IS8000

## Remote waveform monitoring and instrument control

### XWirepuller — Free Software —


Remote control and waveform display monitoring of a DL350 via USB or Ethernet.



## PC data and setup file management

### DL350 Assistant Software — Free Software —


Data files or setup configuration files stored in the DL350 SD card can be backed up with the press of a button. Remote setting, start-stop control and setup file editing can also be easily done on the connected PC.



## Software Control <http://tmi.yokogawa.com/ea/products/oscilloscopes/oscilloscopes-application-software/>

	Free Software	Advanced Software <span style="background-color: yellow; border-radius: 50%; padding: 2px;">Trial version available</span>
Off-line waveform display and analysis	<ul style="list-style-type: none"> <li>XviewerLITE<sup>6</sup>—Basic check— Zoom, V-cursor, conversion to CSV format</li> <li>DIAdem DataPlugin<sup>1</sup></li> </ul>	<ul style="list-style-type: none"> <li>IS8000<sup>4</sup>—Integrated Software Platform—                             <ul style="list-style-type: none"> <li>• Data acquisition<sup>5</sup></li> <li>• Multi-unit monitoring with time synchronization<sup>5</sup></li> <li>• Waveform analysis</li> <li>• File Management</li> <li>• Instrument communication function</li> </ul> </li> <li>Xviewer<sup>6</sup>—Advanced Analysis—                             <ul style="list-style-type: none"> <li>• Waveform analysis</li> <li>• File Management</li> <li>• Instrument communication function</li> </ul> </li> </ul>
Waveform monitoring on a PC	<ul style="list-style-type: none"> <li>XWirepuller Remote monitor and operation, transfer image files</li> </ul>	
Data transfer to a PC	<ul style="list-style-type: none"> <li>DL350 Assistant Software</li> </ul>	
Command control Custom software development	<ul style="list-style-type: none"> <li>Control library “TMCTL” For Visual Studio</li> <li>LabVIEW<sup>3</sup> Instrument Driver</li> <li>WDF File Access Library Access to waveform data (WDF) file</li> <li>MATLAB<sup>2</sup> WDF Access Toolbox Transfer data file to MATLAB</li> </ul>	

\*1: The DataPlugin software can be downloaded from the National Instruments (NI) web site. \*2: MathWorks’s product. \*3: Program development environment provided by National Instruments (NI)  
\*4: Some functions are available free. For details, please refer to BU IS8000-01EN \*5: Supported by DL950 and WT5000, not supported by DL350. \*6: Please note that it cannot be used with DL950.

	AC adapter <b>720921</b>		DC power cable <b>720922</b>		Battery Pack: <b>739883</b> Battery Pack Cover: <b>720923</b>		10:1 Probe <b>702902</b>
	100:1 Probe <b>701947</b>		Safety BNC cable 1 m: <b>701902</b> 2 m: <b>701903</b>		1:1 Safety BNC adapter lead <b>701901</b>		1:1 Safety Adapter Lead For 720268 <b>701904</b>
	Alligator clip adaptor set <b>758929</b>		Clamp-on probe AC 50 A: <b>720930</b> AC 200 A: <b>720931</b> 40 Hz to 3.5 kHz		Scanner box <b>701953</b>		Logic probe (TTL level/contact input) 1 m: <b>702911</b> 3 m: <b>702912</b>
	Bridge head (NDIS) 120 Ω: <b>701955</b> 350 Ω: <b>701956</b>		Bridge head (DSUB) 120 Ω: <b>701957</b> 350 Ω: <b>701958</b>		Carrying case <b>93050</b>		GPS unit* <b>720940</b>

\*The GPS unit can only be supplied to countries where it is not prohibited by local radio laws.

## Specifications (Main unit)

\*For the plug-in modules specifications, see the "Bulletin DL950-02EN".

Main Specifications (Main Unit)	
Type	Plug-in input unit
Number of slots	2
Maximum number of input channels	8 channels (when a 4-CH module is installed in both slots) + the unit standard logic is 16 bit 32 channels (when a 16-CH module is installed in both slots) + the unit standard logic is 16 bit 240 channels (when the 720241 or 720242 module is installed in both slots) + the unit standard logic is 16 bit
Memory capacity	Total 200 Mpoint (100 Mpoint per module)
Recorder Mode Function	
Waveform acquisition and display	
Recording conditions	Recording for a specified time Records data from start for a specified time. Continuous recording Records data until stopped. Start at trigger Records data from a trigger for a specified time. Finish with trigger Records data for a specified time until a trigger.
Acquisition mode	Normal Normal waveform acquisition Envelope The peak values are held at the maximum sample rate regardless of the time axis setting.
Recording time	10 seconds to 50 days
Sampling interval	1 μs to 200 ms (1-2-5 system)
Action when recording is finished	Saves display image data, saves waveform data, sounds a notification buzzer and transfers an e-mail.
Real-time SD card recording	
Binary format	Sampling interval Depends on the number of channels being used. Minimum: 10 μs (when 10 channels are used)* *Sometimes 10 μs or more can be stored depending on the capacity of the SD card. Maximum number of recording points 5 Gpoints (There are limits based on a module being used.) Operation overview Stores data in the binary format when acquisition occurs.
ASCII format	Recording interval 1, 2, 5, 10, 15, 20, 30 s, 1, 2, 5, 10, 15, 20, 30, 60 min. Capacity 2 GByte Operation overview Stores data in the text format at specified intervals
Event recording	Able to record up to 100 events through the event input terminal.
Display time length	1 ms to 10 s (1-2-5 steps), 20 s, 30 s, 40 s, 50 s, 60 s, 100 s, 200 s, 300 s 10 to 60 min (10-min steps), 100 min 2 hours, 5 hours, 10 to 60 hours (10-hour steps), 80 hours, 100 hours 5 days, 10 days, 20 days, 30 days*, 40 days*, 50days* *Only during real-time recording
Zoom	1 window
Display format	1, 2, 3, 4, 5, 6, 8, 12, 16 TY display windows
Maximum number of displayed traces	32 (standard logic: 16 bit, including Math)

X-Y display	The X and Y axes can be selected from analog input waveforms and MATH waveforms (up to 2 traces and 1 window).
Vertical Axis	
Vertical axis setting	It can be set in the measurement range.
Channel on/off	CHn, CHn_m and MATHn can be turned on and off separately.
Vertical axis zooming	You set the scale using upper and lower limits.
Linear scaling	It can be set to AX+ B or P1-P2. (only for voltage, stress, and frequency).
Triggering Section	
Selectable trigger level range	0 ± measurement range
Trigger hysteresis	When measuring voltage: Select form ±1%/±5%/±10% of the range. When measuring temperature: Select form ±0.5°C, ±1.0°C, and ±2.0°C. When measuring strain: Select form ±2.5%/±12.5%/25% of the range. When measuring acceleration: Select form ±1%/±5%/±10% of the range. When measuring frequency: Select form ±0.1%/±5%/±10% of the range. CAN/CAN FD/LIN/SENT: Select form ±0.1%/±5%/±10% of the span width.
Manual trigger	Dedicated key operation
Trigger source	CHn, CHn_m (select an input channel and specify bit for logic), external trigger Time
Trigger type	Edge Rising, falling, or rising or falling. (Rising or falling is unavailable for logic.) Time Date (year, month, and day), time (hour, minute and second) OR The DL350 triggers on the OR of multiple trigger source edges (including a Windows trigger). AND The DL350 triggers on the AND of multiple state conditions (including a Windows trigger).
Analysis	
Cursors	T-Y waveform Horizontal, Vertical, H&V, Marker and Degree X-Y waveform Horizontal, Vertical, H&V and Marker FFT waveform Marker, Peak and Peak List
Automated measurement of waveform parameters	
Parameters	Analog waveform and Math PP, Amp, Max, Min, High, Low, Avg, Mid, Rms, Sdev, +Over, -Over Rise, Fall, Freq, Period, +Width, -Width, Duty, Pulse, Burst1, Burst2, Avg.Freq, Avg.Period, Int1TY, Int2TY, Int1XY, Int2XY, Delay 1 cycle mode
Logic waveform	Freq, Period, Pulse, Duty, Avg.Freq, Delay
Statistical processing	Statistical items: Max, Min, Avg, Sdev, and Cnt Maximum number of cycles: 10000 Maximum measurement range: 100 Mpoint
Cyclic statistical processing	The DL350 automatically measures the waveform parameters of the data and performs statistical processing on the parameters once per period.
Waveform computation	Operators: +, -, ×, ÷, binary computation, frequency, period, moving average (10 points) and RMS Computation length: up to 2 Mpoint (when 1 waveform is used).

FFT	Type: LS, RS, PS, PSD Time windows: Hanning, Hamming, FlatTop, and Rectangle
Harmonic analysis	
Maximum number of simultaneous analysis	Line: 8 channels, power: 1 system
Fundamental wave	50 Hz, 60 Hz or auto setting
FFT points	2048
Analysis order	Fundamental wave to 40th
Window width	10 periods (for 50 Hz), 12 periods (for 60 Hz) or 8 periods (auto)
Types of harmonic analysis	Harmonic RMS value, percentage of content, phase angle, distortion factor (IEC or CSA) and total RMS value
Power analysis	It can be selected from 1P2W (single-phase, two-wire), 1P3W (single-phase, three-wire) or 3P3W (three-phase, three-wire)
Analysis result display	Displays one item selected from 8 line channels and 1 power system Display form: List or bar graph
Analysis result recording	All analysis results can be stored in a media. Data format: CSV

**Scope Mode Function**

**Waveform Acquisition and Display**

Acquisition mode	Normal Normal waveform acquisition
	Envelope The peak values are held at the maximum sample rate regardless of time axis setting.
	Averaging The number of times to average: 2 to 65536 in 2 <sup>n</sup> steps or Infinite (attenuation constant 2 to 256 in 2 <sup>n</sup> step).
Record length	10 k, 25 k, 50 k, 100 k, 250 k, 500 k, 1 M, 2.5 M, 5 M, 10 M, 25 M, 50 M, 100 M (points)
Selectable time scale range	1 $\mu$ s/div to 1 s/div (in 1-2-5 steps), 2 s/div, 3 s/div, 4 s/div, 5 s/div, 6 s/div, 8 s/div, 10 s/div, 20 s/div, 30 s/div 1 min/div to 6 min/div (in 1 min steps), 8 min/div, 10 min/div, 12 min/div, 30 min/div 1 h/div to 6 h/div (in 1 h steps), 8 h/div, 10 h/div, 12 h/div 1 day/div to 5 days/div (in 1 day steps)
Action when recording is finished	Saves display image data, saves waveform data, sounds a notification buzzer and transfers an e-mail.
Real-time SD card recording (binary format)	Sampling interval Depends on the number of channels being used. Maximum: 100 kS/s (when 10 channels are used)* *Sometimes only 100 kS/s or less can be stored depending on the capacity of the SD card. Maximum number of recording points 20 Gpoints (There are limits based on a module being used.) Operation overview Stores data in the binary format when acquisition occurs.
Event recording	Able to record up to 100 events through the event input terminal.
Zoom	2 windows
Display format	1, 2, 3, 4, 5, 6, 8, 12, 16 TY display windows
Maximum number of displayed traces	32 (standard logic: 16 bit, including Math)
X-Y display	The X and Y axes can be selected from analog input waveforms and MATH waveforms (up to 2 traces and 1 window).
History feature	Up to 1000 histories
Accumulation	Waveform overlay (The number of times is limitless.)

**Vertical and Horizontal Control**

Vertical axis setting	Scale/div
Channel on/off	CHn, CHn_m and Mathn can be turned on and off separately.
Vertical axis zooming	$\times 0.1$ to $\times 100$ (varies depending on the module) You set the scale using upper and lower limits or switch between different scales.
Vertical position setting	Waveforms can be moved in the range of $\pm 5$ div.
Linear scaling	It can be set to AX + B or P1-P2 (only for voltage, stress, and frequency).
Roll mode display	Roll mode is enabled when the trigger mode is set to Auto, Single, or On Start, and the time axis setting is greater than or equal to 100 ms/div.

**Triggering Section**

Trigger mode	Auto, Normal (repeat), Single (one-off), or On Start	
Selectable trigger level range	0 $\pm$ 10 div	
Trigger hysteresis	When measuring voltage: Select from $\pm 0.1$ div, $\pm 0.5$ div and $\pm 1$ div. When measuring temperature: Select from $\pm 0.5^\circ\text{C}$ , $\pm 1.0^\circ\text{C}$ and $\pm 2.0^\circ\text{C}$ . When measuring strain: Select from $\pm 2.5\%$ , $\pm 12.5\%$ and $25\%$ . When measuring acceleration: Select from $\pm 0.1$ div, $\pm 0.5$ div and $\pm 1$ div. When measuring frequency: Select from $\pm 0.01$ div, $\pm 0.5$ div and $\pm 1$ div. CAN/CAN FD/LIN/SENT: Select from $\pm 0.01$ div, $\pm 0.5$ div and $\pm 1$ div of the span width.	
Selectable trigger position range	0 to 100% (of the display record length: resolution: 0.1%)	
Selectable trigger delay range	0 to 10 s (resolution: 10 ns)	
Manual trigger	Dedicated key operation	
Simple trigger	Trigger source	CHn and CHn_m (select an input channel and specify bit for logic), EXT, or Time
	Trigger slope	Rising, falling, or rising or falling. (Rising or falling is unavailable for logic.)
	Time trigger	Date (year, month, and day), time (hour, minute and second), and time interval (10 seconds to 24 hours)
Enhanced trigger	Trigger source	CHn, CHn_m (select an input channel and specify bit for logic), EXT
	Trigger type	OR / AND / Wave Window / Edge On A / Period / Pulse Width

**Analysis**

Cursors	T-Y waveform Horizontal, Vertical, H&V, Marker and Degree X-Y waveform Horizontal, Vertical, H&V and Marker FFT waveform Marker, Peak and Peak List
Automated measurement of waveform parameters	
Parameters	Analog waveform and Math PP, Amp, Max, Min, High, Low, Avg, Mid, Rms, Sdev, +Over, -Over Rise, Fall, Freq, Period, +Width, -Width, Duty, Pulse, Burst1, Burst2, Avg.Freq, Avg.Period, Int1TY, Int2TY, Int1XY, Int2XY, Delay, 1 cycle mode Logic waveform Freq, Period, Pulse, Duty, Avg.Freq, Delay
Statistical processing	Statistical items: Max, Min, Avg, Sdv, and Crnt Maximum number of cycles: 10000 Maximum measurement range: There is no restriction on the data in the memory. For SD recording waveforms, up to 100 Mpoint.
Continuous statistical processing	Statistical processing is performed while waveforms are acquired.
History statistical processing	The DL350 automatically measures the waveform parameters of each history waveform and performs statistical processing on the parameters.
Cyclic statistical processing	The DL350 automatically measures the waveform parameters of the data and performs statistical processing on the parameters once per period.
Waveform computation	
Operators: +, -, $\times$ , $\div$ , binary computation, shift, frequency, period, moving average (10 points) and RMS	
Computation length: Up to 2 Mpoint (when 1 waveform is used).	
FFT	
Type: LS, RS, PS, PSD	
Time windows: Hanning, Hamming, FlatTop, and Rectangle	
Average: Time axis and frequency axis	
GO/NO-GO determination: Specified actions are performed on acquired waveforms.	
Zone determination	Determination zone: Up to 6, the number of target waveforms: up to 8, AND or OR determination.
Parameter determination	Determines by the combination of parameters (waveform parameters or harmonic analysis results) up to 8.
Action at the time of determination	Saves display image data, saves waveform data, sounds a notification buzzer and transfers an e-mail.
Harmonic analysis	
Maximum number of simultaneous analysis	Line: 8 channels, power: 1 system
Fundamental wave	50 Hz, 60 Hz or auto setting
FFT points	2048
Analysis order	Fundamental wave to 40th
Window width	10 periods (for 50 Hz), 12 periods (for 60 Hz) or 8 periods (auto)
Types of harmonic analysis	Harmonic RMS value, percentage of content, phase angle, distortion factor (IEC or CSA) and total RMS value
Power analysis	It can be selected from 1P2W (single-phase, two-wire), 1P3W (single-phase, three-wire) or 3P3W (three-phase, three-wire)
Analysis result display	Displays one item selected from 8 line channels and 1 power system Display form: List or bar graph
Analysis result recording	All analysis results can be stored in a media. Data format: CSV

**Time Axis**

Time accuracy	$\pm 0.001\%$
External clock input	Clock input is available through the external-clock input terminal.

**Display**

Display	8.4-inch color TFT LCD (resistive touch panel) Display resolution: 800 (horizontal) $\times$ 600 (vertical)
Display format	T-Y (up to 16 divisions with zoom feature), X-Y, FFT and harmonic analysis
Defective pixels	Within 10 ppm over the total number of pixels including RGB

**Main Unit Standard Logic Input**

Input format	Non-isolated (common to main unit GND) Dedicated probes required (automatic detection)
Compatible probes	700986, 700987, 702911, 702912
Maximum sample rate	10 MS/s
Number of inputs	8 bit $\times$ 2
Chatter suppression	Off, 5 ms, 10 ms, 20 ms, 50 ms, 100 ms

**Data Storage**

Data Storage	
Type of storage data	Measurement data, analysis results, setting values, display images
Storage format of measurement data	Binary format (.WDF), MATLAB format (.MAT) and text format (.CSV) Maximum file size (MAT and CSV formats): 2 GByte
Storage destination	SD card, USB storage and network drive

**Display Image Storage**

Storage format of image data	PNG, JPEG, BMP, monochrome or color
Storage destination	SD card, USB storage and network drive

**Storage**

SD Memory Card	
Number of slots	1
Supported cards	SD, SDHC and SDXC compliant memory cards

USB Storage	
Compatible USB storage devices	Mass storage devices that are compliant with USB Mass Storage Class Ver. 1.1
Available space	Up to 2 TB Partition style: MBR, GPT, format: FAT16, FAT32 and exFAT

#### USB Ports for Peripherals

Connector type	USB type A (receptacle)
Electrical and mechanical specifications	USB Rev. 2.0 compliant
Supported transfer mode	HS (High Speed: 480 Mbps), FS (Full Speed: 12 Mbps), LS (Low Speed: 1.5 Mbps)
Compatible devices	Mass storage devices that are compliant with USB Mass Storage Class Ver. 1.1 104 or 109 keyboards that are compliant with USB HID Class Ver. 1.1 Mouse devices that are compliant with USB HID Class Ver. 1.1 HP ink-jet printers or BrotherPocketJET printers that are compliant with USB Printer Class Ver. 1.0
Number of ports	2
Power supply	5 V, 500 mA (total of the 2 ports)

#### External Printer Output

Compatible models	Mobile printer PocketJET 300 dpi of Brother Industries, Ltd. Ink-jet printer (single-function product) of Hewlett-Packard Company <sup>1</sup>
Output format	Screen hard copy, Detailed waveform print <sup>2</sup>

<sup>1</sup>: Refer to their catalogs or home page <sup>2</sup>: Available only with the Brother's printer

#### Auxiliary I/O Section

##### External Clock Input Terminal

Connector type	Screwless terminal block
Maximum voltage to the ground	Non-isolated (common to main unit GND)
Input level	TTL (0 to 5 V)
Maximum frequency	1 MHz
Minimum pulse width	300 ns
Detected edge	Rising

##### Trigger Input Terminal

Connector type	Screwless terminal block
Maximum voltage to the ground	Non-isolated (common to main unit GND)
Input level	TTL (0 to 5 V)
Minimum pulse width	1 $\mu$ s
Detected edge	Rising or falling
Trigger delay time	Within 1 $\mu$ s + 1 sample period

##### Trigger Output Terminal

Connector type	Screwless terminal block	
Maximum voltage to the ground	Non-isolated (common to main unit GND)	
Output level	5 V CMOS	
Output formats		
Normal format	Logic	Low when a trigger occurs and high after acquisition is completed.
	Output delay	Within 1 $\mu$ s + 1 sample period
	Output hold time	1 $\mu$ s
Pulse format	Logic	Transmits a pulse when a trigger occurs
	Output delay	Within 1 $\mu$ s + 1 sample period
	Pulse width	1 ms, 50 ms, 100 ms, 500 ms
Sample pulse format	Logic	Transmits pulses at a given frequency during waveform acquisition
	Frequency range	5 Hz to 200 kHz (1-2-5 steps)
Start/Stop	Logic	High level output during waveform acquisition

##### GO/NO-GO Determination Output

Connector type	Screwless terminal block
Maximum voltage to the ground	Non-isolated (common to main unit GND)
Output level	5 V CMOS

##### External Start/Stop Input

Connector type	Screwless terminal block
Maximum voltage to the ground	Non-isolated (common to main unit GND)
Input level	TTL (0 to 5 V) or contact

##### Event Input

Connector type	Screwless terminal block
Maximum voltage to the ground	Non-isolated (common to main unit GND)
Input level	TTL (0 to 5 V) or contact

##### COMP Output (Probe-compensation-signal output terminal)

Output signal frequency	1 kHz $\pm$ 1%
Output amplitude	1 V <sub>p-p</sub> $\pm$ 10%

##### GPS Interface

Input connector	Mini DIN 9-pin
Compatible GPS unit	720940 optional accessories (sold separately)

#### Computer Interface

##### USB-PC Connection

Connector type	USB type B (mini)
Electrical and mechanical specifications	USB Rev. 2.0 compliant
Supported transfer mode	HS (High Speed: 480 Mbps) and FS (Full Speed: 12 Mbps)
Supported protocols	USBTMC-USB488 (USB Test and Measurement Class Ver. 1.0) <sup>1</sup> Mass Storage Class Ver. 1.1 (target: SD card)
PC system requirements	Windows 8.1, Windows 10, Windows 11

#### Ethernet

Connector type	RJ-45 modular jack
Ports	1
Electrical and mechanical specifications	IEEE802.3
Transmission system	Ethernet (100BASE-TX, 10BASE-T)
Communication protocol	TCP/IP
Supported services	DHCP, DNS, SNMP client, SMTP client, FTP client, VXI-11, and Web server

\*1: A separate driver is required.

#### General Specifications

Standard operating conditions	Ambient Temperature: 23 $\pm$ 5°C Ambient humidity: 20 to 80% RH After the DL350 has been warmed up for 30 minutes and then calibration has been performed
Recommended calibration period	1 year
Warm-up time	At least 30 minutes
Operating environment	Temperature: 0 to 45°C (While an AC adapter is working: 0 to 40°C, while a battery is being charged: 0 to 35°C) Humidity: 20 to 85% RH (no condensation) Altitude: 2000 m or less
Storage environment	Temperature: -20 to 60°C Humidity: 20 to 85% RH (no condensation)
Power supply	The DL350 operates on the AC adapter (720921), DC power input (720922) or the battery pack (739883). *Operation of the battery pack requires the battery pack cover (720923). AC adapter or DC input has priority if those input and battery are available

##### AC adapter (720921)

Rated supply voltage	100 to 240 VAC
Permitted supply voltage range	90 to 264 VAC
Rated supply frequency	50 or 60 Hz
Permitted supply voltage frequency range	47 to 63 Hz
Maximum power consumption	120 VA
Withstand voltage	3 kV (between the main unit and AC adapter power line)
Insulation resistance	10 M $\Omega$ (between the main unit and AC adapter power line)

##### DC power input (720922)

Rated supply voltage	10 to 30 VDC (at the DL350 connector end)
Maximum power consumption	45 W
Standby power (when the power is turned off or charging is stopped)	0.6 Wtyp

##### DC power cable

	Cigarette lighter plug Type, length: 2.5 m
--	--

##### Battery pack (739883)

Type	Lithium-ion
Operation time	Approx. 3 hours
Charge time	Approx. 6 hours (When the DL350 is turned off.)

Installation position	Vertical orientation installation, horizontal orientation installation or inclined installation
-----------------------	---

External dimensions	Approx. 305 mm (W) $\times$ 217 mm (H) $\times$ 92 mm (D) (not including the protrusions)
---------------------	---

Weight	Approx. 3.9 kg (when the DL350 equipped with the battery and 2 pieces of 720254.)
--------	---

Instrument cooling method	Forced air cooling (exhaust)
---------------------------	------------------------------

Battery backup	The settings and clock are backed up with an internal lithium battery. Life: Approx. 5 years (at an ambient temperature of 23°C)
----------------	--

Safety standard	Compliant standards EN61010-1, EN IEC61010-2-030, EN61010-031, EN60825-1 Pollution degree 2, Indoor use Measurement Category: See the specifications of each module.
-----------------	---

Emissions	Compliant standards EN61326-1 Class A, EN61326-2-1, EN55011: Class A, Group 1 EMC Regulatory Arrangement in Australia and New Zealand EN55011 Class A, Group 1 Korea Electromagnetic Conformity Standard
-----------	--

Immunity	Compliant standards EN61326-1 Table 2 (for use in industrial locations), EN61326-2-1
----------	---

Standard of resistance against vibration	JIS D 1601:1995 5.2 5.3 (1) Type 1: Type A compliant
--	--

#### GPS unit (720940) Specifications

Receiver type	GPS/GLONASS/QZSS/SBAS (MSAS/WAAS/EGNOS/GAGAN)
Function	GPS data acquisition (latitude, longitude, altitude, speed, moving direction and GPS information), DL350 time synchronization
Measurement accuracy <sup>*1</sup>	Horizontal position: 15 m or less (GPS information/SA=OFF/PDOP $\leq$ 3) Speed: 1 m/s (GPS information/SA=OFF/PDOP $\leq$ 3)
Following performance	Altitude: -500 to +18000 m Speed: 1800 km/h or less Acceleration: 2 G or less
Measurement resolution	Latitude and longitude: 1 $\mu$ ° Altitude: 0.1 m, 1 m Speed: 0.01 km/h, 0.1 km/h Direction: 0.01°

\*1: The specification values may not be attained depending on the measurement location, environment and measurement time.

## Model and suffix code

Model	Suffix Code	Description
DL350		DL350 ScopeCorder (Plug-in modules and AC adapter are not included.)
Languages	-HJ	Japanese menu
	-HE	English menu
	-HC	Chinese menu
	-HK	Korean menu
	-HG	German menu
	-HF	French menu
	-HL	Italian menu
	-HS	Spanish menu
	-HR	Russian menu
Options	/VE	Vehicle Edition
	/EB	Battery pack + Battery pack cover 60 W AC Adapter
720921		<b>AC adapter (Separate purchase) is required to charge the battery and operate the main unit.</b>
Power cord	-D	UL/CSA Standard
	-F	VDE/Korean Standard
	-Q	BS/Singapore Standard
	-H	GB Standard
	-T	BSMI Certification
	-N	NBR Standard

Standard accessories: Hand strap, Slot cover panel (2), User's manual

## DC power cable and Battery Pack Accessories

Model	Suffix Code	Description
720922		DC cable (Cigarette lighter plug Type)
739883		Battery Pack <sup>1, 2, 3</sup>
720923		Battery Pack Cover <sup>3</sup>

\*1: AC adapter (720921) is required for charging battery.

\*2: Operation of the battery pack (739883) requires the battery pack cover (720923)

\*3: Included in the /EB option.

## Plug-in module model numbers

Model	Description
720211	High-speed 100 MS/s 12-Bit Isolation Module (2 ch)
720250	High-speed 10 MS/s 12-Bit Isolation Module (2 ch)
720254	4-CH 1 MS/s 16-Bit Isolation Module
720268	High-Voltage 1 MS/s 16-Bit Isolation Module (with AAF, RMS)
720220	Voltage Input Module (16 ch)
701261	Universal Module (2 ch)
701262	Universal Module (with Anti-Aliasing Filter, 2 ch)
701265	Temperature/High-Precision Voltage Module (2 ch)
720266	Temperature/High-Precision Voltage Isolation Module (Low noise)
720221	16-CH Temperature/Voltage Input Module
701953-L1	16-CH Scanner Box (provided with 1 m cable)
701953-L3	16-CH Scanner Box (provided with 3 m cable)
701270	Strain Module (NDIS, 2 ch)
701271	Strain Module (DSUB, Shunt-CAL, 2 ch)
701275	Acceleration/Voltage Module (with Anti-Aliasing Filter, 2 ch)
720281	Frequency Module (2 ch)
720230	Logic Input Module (16 ch)
720245	CAN FD/LIN Monitor Module
720243	SENT Monitor Module

\*Probes are not included with any modules.

The /VE option is required when using the 720245 or 720243 module.

The use of a 720221 module always requires the External Scanner Box (model 701953).

## IS8000 model numbers

Model	Description
IS8001	IS8000 Integrated Software Platform Subscription (Annual license)
IS8002	IS8000 Integrated Software Platform Perpetual (Permanent license)

\*See BU IS8000-01EN for option.

## Additional Option License\*1

Model	Suffix Code	Description
709830	-VE	Vehicle Edition

\*1: Separately sold license product (customer-installable).

## Probes, cables and converters

Model	Product	Description <sup>1</sup>
702902	10:1 Probe (for isolated BNC input)	Operating temp. range: -40 to 85°C, length 2.5 m
701947	100:1 Probe (for isolated BNC input)	1000 V (DC+ACpeak) CAT II
700929	10:1 Probe (for isolated BNC input)	1000 V (DC+ACpeak) CAT II, length 1.5 m
701901	1:1 Safety BNC adapter lead	1000 Vrms-CAT II
701904	1:1 Safety Adapter Lead (in combination with followings)	1000 Vrms-CAT II, 600 Vrms-CAT III
758928	Pincher tip (Hook type)	1000 Vrms-CAT III, 1 set each of red and black
701954	Large alligator-clip (Dolphin type)	1000 Vrms-CAT III, 1 set each of red and black
758929	Alligator clip adaptor set (Rated voltage 1000 V)	1000 Vrms-CAT II, 1 set each of red and black
758922	Alligator clip adaptor set (Rated voltage 300 V)	300 Vrms-CAT II, 1 set each of red and black
758921	Fork terminal adaptor set	1000 Vrms-CAT II, 1 set each of red and black
701940	Passive probe <sup>2</sup>	Non-isolated 600 Vpk (10:1)
366926	1:1 BNC-alligator cable	Non-isolated 42 V or less, 1 m
366961	1:1 Banana-alligator cable	Non-isolated 42 V or less, 1.2 m
720930	Clamp-on probe	AC 50 A, 40 Hz to 3.5 kHz
720931	Clamp-on probe	AC 200 A, 40 Hz to 3.5 kHz
701955	Bridge head (NDIS, 120 Ω)	With 5 m cable
701956	Bridge head (NDIS, 350 Ω)	With 5 m cable
701957	Bridge head (DSUB, 120 Ω)	Shunt-CAL with 5 m cable
701958	Bridge head (DSUB, 350 Ω)	Shunt-CAL with 5 m cable
702911	Logic probe <sup>3</sup>	8-Bit, 1 m, non-Isolated, TTL level/Contact Input
702912	Logic probe <sup>3</sup>	8-Bit, 3 m, non-Isolated, TTL level/Contact Input
700986	High-speed logic probe <sup>3</sup>	8-Bit, non-Isolated, response speed: 1 μs (typ.)
700987	Isolated logic probe <sup>4</sup>	8-Bit, each channel isolated
701902	Safety BNC-BNC cable (1 m)	1000 Vrms-CAT II (BNC-BNC)
701903	Safety BNC-BNC cable (2 m)	1000 Vrms-CAT II (BNC-BNC)
720940	GPS unit <sup>5</sup>	For DL350
705926	Connecting cables	Connecting cable for 701953 (1 m)
705927	Connecting cables	Connecting cable for 701953 (3 m)
93050	Carrying Case	

\*1: Actual allowable voltage is the lower of the voltages specified for the main unit and cable.

\*2: 30 Vrms is safe when using the 701940 with an isolated type BNC input.

\*3: Includes one each of the B9879PX and B9879KX connection leads.

\*4: Additionally, 758917 and either the 758922 or 758929 are required for measurement.

\*5: The GPS unit can only be supplied to countries where it is not prohibited by local radio laws.

This is a Class A instrument based on Emission standards EN61326-1 and EN55011, and is designed for an industrial environment. Operation of this equipment in a residential area may cause radio interference, in which case users will be responsible for any interference which they cause.

### NOTICE

- Before operating the product, read the user's manual thoroughly for proper and safe operation.

ScopeCorder, **GIGAzoom**, **ISOPRO** are registered trademarks of Yokogawa Electric Corporation.

\*Any company's names and product names mentioned in this document are trade names, trademarks or registered trademarks of their respective companies.  
The User's Manuals of this product are provided by CD-ROM.

### Yokogawa's approach to preserving the global environment

- Yokogawa's electrical products are developed and produced in facilities that have received ISO14001 approval.
- In order to protect the global environment, Yokogawa's electrical products are designed in accordance with Yokogawa's Environmentally Friendly Product Design Guidelines and Product Design Assessment Criteria.

# YOKOGAWA

YOKOGAWA TEST & MEASUREMENT CORPORATION  
Global Sales Dept. /E-mail: tm@cs.jp.yokogawa.com

YOKOGAWA CORPORATION OF AMERICA  
YOKOGAWA EUROPE B.V.  
YOKOGAWA TEST & MEASUREMENT (SHANGHAI) CO., LTD.  
YOKOGAWA ELECTRIC KOREA CO., LTD.  
YOKOGAWA ENGINEERING ASIA PTE. LTD.  
YOKOGAWA INDIA LTD.  
YOKOGAWA ELECTRIC CIS LTD.  
YOKOGAWA AMERICA DO SUL LTDA.  
YOKOGAWA MIDDLE EAST & AFRICA B.S.C(c)

<https://tmi.yokogawa.com/>

YMI-N-MI-M-E03

The contents are as of September 2023. Subject to change without notice.  
Copyright © 2017, Yokogawa Test & Measurement Corporation  
[Ed: 07/b] Printed in Japan, 309(KP)

<https://tmi.yokogawa.com/us/>  
<https://tmi.yokogawa.com/eu/>  
<https://tmi.yokogawa.com/cn/>  
<https://tmi.yokogawa.com/kr/>  
<https://tmi.yokogawa.com/sg/>  
<https://tmi.yokogawa.com/in/>  
<https://tmi.yokogawa.com/ru/>  
<https://tmi.yokogawa.com/br/>  
<https://tmi.yokogawa.com/bh/>